

32 Port Enterprise Class 4 Digital Pathway Multi-user Cat5 KVM Matrix Switch over IP

Details	StarTech.com	Tripp Lite	Avocent	Raritan
Model	SV3254DX4I	B064-032-04-IP	DSR2035	KX2-432
MSRP	\$4,399.00	\$6,600.00	\$4,995.00	\$7,195.00
Concurrent IP Users	4	4	2	4
# of ports:	32	32	32	32
RJ-45	✓	✓	✓	✓
Features				
Full USB 2.0 Virtual media	✓	-	-	-
Multi-User (Matrix) support	✓	✓	✓	✓
CAT5 connections to servers	✓	✓	✓	✓
Crash Cart Ports	✓	-	-	-
Virtual Media for each connected server	✓	✓	✓	✓
Storage over USB	✓	✓	✓	✓
Transfer files between servers	✓	✓	-	✓
Out-of-Band (Modem accessibility)	✓	✓	✓	✓
Native VNC Support	✓	-	-	-
Linux Open Source	✓	-	-	-
Webbrowser GUI Interface	✓	✓	✓	✓
Remote user station** (up to 1000 ft. away)	✓	-	-	-
Independent WAN and LAN ports	✓	-	-	-
Dongle firmware auto-update	✓	-	-	-
Front and Rear video connections	✓	-	-	-
USB & PS2 ports on unit	✓	✓	✓	✓
Max. Resolution	1600 x 1200 @ 75 Hz	1600 x 1200 @ 60 Hz	1280 x 1024 @ 75 Hz	1600 x 1200
Max. Users connected over IP	5	4	2	8
Connect to USB PCs	✓	✓	✓	✓
Connect to PS/2 PCs	✓	✓	✓	✓
Max. Distance from each Server***	164'	30'	30'	150'
Perfect Mouse Synchronization*	✓	-	-	✓
External Unit Reset	✓	-	-	-
OSD (Onscreen display)	✓	✓	✓	✓
Protocols				
VT100/102 Terminal Emulator built-in	✓	✓	✓	✓
SSL, SSH, Telnet, TIP	✓	✓	✓	✓
HTTP, HTTPS	✓	✓	✓	✓
SNMP	✓	✓	✓	✓
RADIUS	✓	-	-	-
Power				
Built-in Cooling Fan(s)	✓	✓	✓	✓
Voltage Support	85-260 VAC	100-240 VAC	100-240 VAC	100-240 VAC
Operating Temperature	32° - 104°F	32° - 122°F	32° - 122°F	32° - 104°F
Max. Consumption	30 W	?	40 W	?
Warranty				
Parts & Labour	2 Years	1 Year	2 Years	2 Years
Lifetime technical Support	✓	✓	✓	✓

MADE IN NORTH AMERICA

For complete product information
Visit www.startech.com/SV3254DX4I

Last updated on March 11th, 2009

Fast, Friendly Support your way!



Phone Support
1-800-265-1844



Email Support
sales@startech.com



Chat Online
www.startech.com

