

VGA Video Splitter (Wall Mountable)

Distribute and deliver your content with two, four and eight port VGA video splitters from Converge A/V. Use a single VGA source to display on multiple monitors simultaneously. Perfect for retail, tradeshow, education, government, and corporate displays where high quality video is required.

The ST122W, ST124W and ST128W support resolutions up to 1600 x 1200 and lets you locate screens up to 200 ft away from your system, plus easy plug and play installation lets you take your show anywhere and set up in seconds.

Rely on Converge A/V products for all your Audio/Video and Digital Signage needs.

The StarTech.com
Advantage:

- Multiple screens let you communicate your message to large audiences with greater impact
- Unit can sit flat, or be wall mounted

Features

- Cascadable up to 3 levels to provide up to eight video signals
- Compact design with convenient topside connection, lays flat or mounts on the wall
- Supports Distances up to 200ft
- Supports resolutions up to 1600x1200.

Applications

- In-store product merchandising
- Information booths/kiosks
- Trade-shows
- Lecture halls and classrooms
- Airports, bus terminals and train stations

Specifications

- 1 Year warranty
- Connector Types: 2 DB15 High Density Female
- Connector Types: 1 DB15 High Density Male
- Maximum Video Resolutions: 1600 x 1200
- VGA Bandwidth: 250 MHz
- Max Distance: Up to 65m / 200ft

CONVERGEAV



Comparison Matrix

	StarTech.com	Cables To Go	Black Box
Wall Mountable	✓		
Easy Port Access	✓		
Supports 1600 x 1200 Resolutions	✓	✓	✓
200 ft. Distance	✓	✓	✓
250 MHz Bandwidth	✓	✓	✓
Lower Price Point	✓		
Two Port	ST122W	29550	AC1056A-2
Four Port	ST124W	29551	AC1056A-4
Eight Port	ST128W	Not Available	AC1056A-8

Solution Diagram

