

10 ft IEEE-1394 FireWire Cable 6-6 M/M

StarTech ID: 1394_10



This 10ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 6 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Gray
- Product Length: 10 ft [3.05 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 120
- Shipping (Package) Weight: 0.46 lb [0.21 kg]

