

10 ft IEEE-1394 Firewire Cable 4-4 M/M

StarTech ID: 1394_44_10



This IEEE 1394 FireWire 400 Cable features two FireWire (4-pin) male connectors and supports full FireWire 400 data transfer rates of up to 400Mbps, to provide a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Backed by StarTech.com's Lifetime Warranty, this cable is expertly designed and constructed of only IEEE-1394 rated wire for full FireWire 400 compatibility and reliability.

Technical Specifications

- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 4 pin Male
- Color: Black
- Product Length: 10 ft [3.05 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 120
- Shipping (Package) Weight: 0.33 lb [0.15 kg]