

15 ft IEEE-1394 Firewire Cable 4-4 M/M

StarTech ID: 1394_44_15



This 15ft 1394 FireWire (400) Cable features two 1394 (4-pin) male connectors and supports full FireWire 400 data transfer rates of up to 400Mbps, to provide a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Backed by StarTech.com's Lifetime Warranty, this cable is expertly designed and constructed of only IEEE-1394 rated wire for full FireWire 400 compatibility and reliability.

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 4 pin Male
- Color: Black
- Product Length: 15 ft [4.57 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 100
- Shipping (Package) Weight: 0.38 lb [0.17 kg]

