

6 ft. Transparent IEEE-1394 Firewire Cable 4-6 Pin

StarTech ID: 1394_46_6T



Capable of transferring data at speeds up to 400 Mbits/sec, this 6 foot, 4-to-6 pin FireWire cable provides the high-speed link required for today's demanding FireWire peripherals. With thi IEEE 1394 rated cable, you'll be able to transfer video from your digital camcorder to your laptop at incredible speeds. This cable features a transparent sheath to quietly blend into any environment and is compatible with all FireWire and iLink devices that require a 4-pin to 6-pin connector.

Applications and Solutions

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

Features

- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Hot Pluggable; allows swapping of live devices
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference
- Supports a daisy-chain of up to 63 firewire devices
- Supports Plug and Play
- Transparent color blends into any environment
- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Up to 400 Mbits/sec data transfer rate

Technical Specifications

- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Transparent
- Product Length: 6 ft [1.83 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 150
- Shipping (Package) Weight: 0.22 lb [0.1 kg]
- Connector A: 4-pin Male
- Connector B: 6-pin Male
- Color: Transparent
- Length: 6ft (1.8m)
- IEE1394-1995 Compliant: