


10 ft 1394b Firewire Cable 9-9 Pin M-M

StarTech ID: 1394_99_10



If your computer's equipped with FireWire 800, you're obviously passionate about speed and performance. Make sure you get the most out of FireWire 800 with quality cables from StarTech.com. These 9-pin cables will keep your high-bandwidth video or graphic applications moving data at up to 800 Mbits/sec, enough for demanding high-speed digital storage and serious video capture. Our FireWire 800 cables come with the highest quality shielding to protect your data and are backed by our lifetime warranty.

Applications and Solutions

- Connect multiple FireWire 800(1394b) compliant devices together
- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products

Features

- 9-pin cable draws power from FireWire bus
- Compatible with all 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Compliant with FireWire800 and 1394b standards
- Fast data transfer rate of up to 800 Mbits/sec
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Supports a daisy-chain of up to 63 fireWire devices
- Twisted Pair Construction

Technical Specifications

- Connector A: 1 - Firewire 800 9 pin Male
- Connector B: 1 - Firewire 800 9 pin Male
- Color: Black
- Product Length: 10 ft [3.05 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 50
- Shipping (Package) Weight: 0.55 lb [0.25 kg]
- Cable Length: 10 Feet (3 Meters)
- Connector A: 1394b 9 pin Male
- Connector B: 1394b 9 pin Male
- Compliant Standard: FireWire 800 & 1394b
- Color: Black