

## 1U DuraView Modular LCD KVM Rack Console with 15 in. TFT Screen

StarTech ID: 1UCABCONS



This 1U Rackmount LCD KVM Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet storage space - a space efficient-solution that provides total KVM control right from a server rack.

The KVM Console combines a 19in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable, compactable design. When the console is not in use, it's as simple as folding the display and keyboard/mouse up (like a laptop computer) and sliding it back into the server rack on the sturdy mounting rails (included).

A highly scalable solution, the LCD console features a modular design that lets you install a multi-port KVM switch directly into the back of the console, allowing you to control multiple servers from a single point while only taking up 1U of rack space.

To simplify maintenance and ensure long-lasting performance, the console keyboard and touch pad are both replaceable - allowing you to swap out components as needed, without replacing the entire console.

### Applications and Solutions

- Centralized control of dozens of PCs and servers if used with optional KVM modules.
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

## Features

- 15 Inch TFT LCD Display
- Full 105 key low profile keyboard
- Modular design allows optional 8 or 16 port KVM switch modules to be integrated into the unit.
- Standard 19" 1U rack drawer
- Supports resolution up to 1024x768 pixels
- Extendable rails can be adjusted between 67.5 cm (26.63 in) and 80.5 cm (36.63 in)
- Quick and easy installation

## Technical Specifications

- Connector Types: 2 - 6 DIN Female
- Connector Types: 1 - High Density DB15 Female
- Enclosure Type: Steel
- Audio Support: No
- KVM Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 1
- Rack-Mountable: Yes
- KVM TFT: 15
- Product Length: 18.9 in [48 cm]
- Maximum Number of Users: 1
- Operating Temperature: 0 to +50°C [32 to 122°F];
- Power Adapter Included: Yes
- Power Adapter - Amperage: 4 Amps
- Power Adapter - DC Voltage: 12 Volts
- Carton Quantity: 1
- Storage Temperature: -20 to +60°C [-4 to 140°F];
- Shipping (Package) Weight: 32.69 lb [14.79 kg]
- LCD Size: 15.1 inches TFT
- Resolution: 1024 x 768 @60/70/75Hz
- Display Color: 16.7M (8 bits)
- User Control: OSD control (auto saving)
- Input Signal: RGB analog, H/V separate

- Plug and Play VESA: VESA DDC 1/2B
- Keyboard: 105 Key, PS/2
- Mouse Touch Pad: PS/2
- Power Management: VESA DPMS compliant
  - ON mode = 23.2W
  - STANDBY mode  $\leq$  1W
  - SUSPEND mode  $\leq$  1W
  - OFF mode  $\leq$  1W
- Cert: FCC (Part 15)
- Rack/Cabinet Depth Requirement: 30 in. (minimum)