


10m Multimode 50/125 Duplex Fiber Patch Cable LC - SC

StarTech ID: 50FIBLCSC10



This 10m LC/SC Duplex 50/125 Multimode Fiber Patch Cable provides the necessary connection between fiber networking devices for high-speed, long distance networks.

Ensuring optimal data transfers and network stability, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Duplex 50/125 Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Applications and Solutions

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Features

- Attenuation loss meets or exceeds industry standards
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty
- Immune to electricity interference

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 2 - Fiber Optic LC Male
- Connector B: 2 - SC Fiber Male
- Color: Orange
- Fiber Size: 50/125
- Fiber Type: Multi Mode
- Product Length: 32.8 ft [10 m]
- Carton Quantity: 64
- Shipping (Package) Weight: 0.15 lb [0.07 kg]
- Cable Length: : 10m (32.8 ft)
- Cable Type: : Duplex Multimode
- Fiber Size: : 50/125 micron
- Connectors: :
- Connector A: LC (male)
- Connector B: SC (male)

