

**330 Watt Silent ATX12V PC Computer Power Supply with 120mm Fan**  
*StarTech ID: ATXPOW330HS*



This 330 Watt ATX12V power supply offers whisper-quiet performance and provides guaranteed compatibility with many 3GHz and faster Intel and AMD processors as well as a broad selection of eMachines and other Gateway systems.

The power supply features a TX3 fan sensor and 12cm dual ball-bearing fan that automatically adjusts speeds as you work, providing superior cooling for your entire system.

Backed by 2 year warranty, StarTech.com's 330 Watt ATX12V power supply is designed to provide dependable power for your hard working PC.

## Applications and Solutions

- **T-Series (cont'd):**T2200, T2200SE, T2240, T2245, T2260, T2341, T2385, T2460, T2482, T2484, T2542, T2596, T2605, T2615, T2625, T2642
  - Compatible with following **eMachines A-Series Model:**  
A26EV17F
    - Compatible with following **eMachines C-Series Models:**C1641, C1844, C1904, C2160, C2280, C2480, C2684, C2685, C2782, C2825
      - Compatible with following **eMachines D-Series Models:**  
D2046, D2244, D2246, D2266, D2346, D2386, D2586, D2685
        - Compatible with following **eMachines H-Series Models:**  
H2341, H2482, H2542, H2602, H2615, H2642, H2742, H2825, H2
          - Compatible with following **eMachines S-Series Models:**S1642, S1862, S1940, S2482, S2485
            - Compatible with following **eMachines T-Series Models:**T1140, T1150, T1220, T1221, T1300, T1360, T1440, T1600, T1740, T1742, T1782, T1840, T1842, T1860, T1862, T1980, T2040, T2042, T2080, T2082, T2085
              - Compatible with following **eMachines W-Series Models:**W1500, W1640, W1700, W1800, W2040, W2047, W2060, W2247, W2060, W2247, W2260, W2646, W2686, W2785, W2958, W4682, W4065
                - Compatible with following **Gateway Models:**  
DX100, B330
                  - More **T-Series:**T2672, T2682, T2692, T2698, T2778, T2792, T2796, T2798, T2824, T2825, T2842, T2865, T2875, T2882, T2885, T2895, T3025, T3265, T4060, T4080, T4170, T4480, T4510, T4511, T4697, T6000
                    - Provides the additional current required by 3 GHz and faster CPUs
                    - Replacement for standard 250W & 300W ATX12V Power Supplies
                    - Replacement Power Supply for **Bestec ATX-300-12E**

## Features

- ATX version 2.03, ATX12V and Serial ATA 1.0 compliant
- High airflow 12cm dual ball bearing fan delivers efficient cooling for the entire system
- High quality connectors provide minimal resistance and enhanced electrical conductivity
- Includes power connectors for Serial ATA Devices
- Industry's leading safety approval ratings
- Premium EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- Provides a maximum output power of 330 watts
- Quad Protection Plus: Short Circuit Protection, Over Voltage Protection, Over Load Protection, Over Current Protection, and No Load Operation.

## Technical Specifications

- Warranty: 2 Year warranty
- Air Flow Rate: 62.4
- Connector Types: 1 - ATX 20 pin Female
- Connector Types: 6 - LP4 Female
- Connector Types: 2 - SP4 Female
- Enclosure Type: Steel
- Fan Bearing Type: Ball Bearing
- Product Height: 3.35 in [8.5 cm]
- Input Current: 4 - 8
- Input Voltage: 240 AC
- Input Voltage: 120 AC
- Input Voltage Frequency: 50 - 60
- Product Length: 5.91 in [15 cm]
- MTBF: 100,000 Hrs
- Noise Level: 19 - 24
- Fans: 1 - 120 mm
- Current -12.0V (A): 0.8
- Current -5.0V (A): 0.5
- Current +12.0V1 (A): 15
- Current +3.3V (A): 28

- Current +5.0V (A): 35
- Current +5.0Vsb (A): 2.5
- Output Power: 330
- Carton Quantity: 10
- Shipping (Package) Weight: 4.35 lb [1.97 kg]
- Product Weight: 4.5 lb [2.03 kg]
- Product Width: 5.51 in [14 cm]

