

## 350 Watt ATX12V 2.01 Dell Replacement Computer PC Power Supply

StarTech ID: ATXPW350DELL



This 350 Watt ATX12V 2.01 Dell PC Power Supply is a reliable upgrade or replacement for many compatible Dell computers (see compatible models below). It offers dual 12V power rails to deliver stable power to demanding components, as well as both 20 and 24-pin ATX motherboard power connectors and a generous number of component connectors to ensure broad system compatibility.

Constructed of high quality components and designed to provide a long-lasting, durable power source for hard-working PCs, the 400 Watt ATX12V 2.01 Dell PC Power Supply is backed by StarTech.com's 2 year warranty and free lifetime technical support.

**Dimension Series Models:** 3000 / 3100 / 4600 / 4700 / 9100 / E310 / E510

**Optiplex Series Model:** GX280

**Power Edge Series Model:** SC420

**Precision Workstation Series Model:** Model 370

### Applications and Solutions

- Replacement 350W power supply, compatible with certain Dell PC's(see model list on Overview page)
- Upgrade current Dell power supply for more power and support of upgraded 24-pin motherboards and SATA hard drives.

## Features

- 20/24 split motherboard connector
- 80mm fan provides efficient cooling for the system and the power supply
- ATX12V version 2.01 compliant
- EMI/RFI power filtration system provides low noise/ripple for super clean and stable power to all system components
- High quality connectors provide minimal resistance and enhanced electric conductivity
- Our power supplies are compatible with many of latest Intel P4 and AMD processors
- SATA connectors for SATA Hard Drive support

## Technical Specifications

- Warranty: 2 Year warranty
- Connector Types: 1 - Split 24/20 pin ATX Motherboard
- Connector Types: 3 - LP4 Female
- Connector Types: 1 - SP4 Female
- Connector Types: 2 - SATA Power Female
- Connector Types: 1 - P4 ATX Male 12V Plug
- Connector Types: 1 - AUX Power 6-pin Female
- Fan Bearing Type: Sleeve Bearing
- Product Height: 3.39 in [86 mm]
- Input Current: 8 ~ 4
- Input Voltage Frequency: 50~60 Hz
- Product Length: 5.91 in [150 mm]
- MTBF: 100000
- Fans: 1 - 80 mm
- Operating Temperature: 0° ~ 50°
- Current -12.0V (A): 0.8A
- Current +12.0V1 (A): 10A
- Current +12.0V2 (A): 15A
- Current +3.3V (A): 22A
- Current +5.0V (A): 21A
- Current +5.0Vsb (A): 2.5A
- Output Power: 350

- Carton Quantity: 6
- Storage Temperature: -20° ~ 80°
- Shipping (Package) Weight: 4.69 lb [2.12 kg]
- Product Weight: 4.2 lb [1.9 kg]
- Product Width: 5.51 in [140 mm]
- General Specifications: Zinc-plated casing
- New Input Voltage: 115 ~ 230

