

100 ft Black Molded Cat6 UTP Patch Cable - ETL Verified

StarTech ID: C6PATCH100BK



StarTech.com's Cat6 UTP Patch Cables offer reliable Ethernet connections. This 100 ft cable is ETL verified to meet or exceed all Category 6 performance standards and features a durable black jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat6 UTP Patch Cables offer PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

StarTech.com's 100 ft Black Cat6 UTP Patch Cable is constructed of only top quality materials to ensure optimum durability and is backed by our Lifetime Warranty.

Applications and Solutions

- Connects workstation to wall outlet
- May be used with gigabyte networks
- Patches from hub to distribution panel

Features

- Coloured Hoods for departmental colour coding
- StarTech Category 6 patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
- StarTech Category 6 Patch cables are constructed with top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - RJ45 Male
- Connector B: 1 - RJ45 Male
- Color: Black
- Product Length: 99.97 ft [30.48 m]
- Maximum Cable Length: 328 ft [100 m]
- Network Cable Type: Molded
- Carton Quantity: 15
- Shipping (Package) Weight: 2.59 lb [1.17 kg]
- Connectors: RJ45 Male, RJ45 Male
- Length: 100 ft
- Rating: 1000X Cat 6 (4 PR 24AWG CSA TIA/EIA-568B)

