

16 Port KVM Switch Module for 1UCABCONS Command Console

StarTech ID: CAB1631D



The CAB1631D is a 16-port add-on KVM module for our popular 1UCABCONS cabinet console. The CAB1631D KVM switch allows up to 16 computers to be directly controlled from the 1UCABCONS console. The combination of these two products offers the latest, most space efficient way to control server rooms and multiple computers.

Note: This product is designed for use with Startech.com's 1UCABCONS and 1UCABCONS17 consoles only

The CAB1631D allows for one user console access. This means that one user may manage multiple computers from a single location. Additional CAB1631D modules can be cascaded to allow up to 136 computers to be controlled. Computers can be selected and switched to from the on-screen display (OSD) menu for fast, efficient, user-friendly control.

Note: The local console ports on this product are designed for diagnostic purposes only. They cannot be used with an external mouse and keyboard or a Server Remote Control unit.

Applications and Solutions

- Co-location/ISP computer control
- Datacenter computer control
- Manufacturing line computer control
- PC test/burn-in computer control

Features

- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during power outage even if it loses power, retaining mouse control.
- An industry first 3-year warranty provides peace of mind.
- Built-in OSD security keeps unwanted users out.
- Can be cascaded to control up to 136 PCs
- Compatible with all notebook computers.
- Compatible with HP/Compaq Alpha systems.
- Completely operating system independent. No software or drivers required
- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems
- Each PC name is user-definable via the OSD menu
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected systems.
- Rugged, all-metal chassis for use in harsh environments and space-saving cabinets.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch

Technical Specifications

- Color: Black
- Connector Types: 1 - 8 DIN Female
- Connector Types: 34 - 6 DIN Female
- Connector Types: 2 - High Density DB15 Female
- Connector Types: 16 - High Density DB15 Male
- Connector Types: 1 - Centronics 50 Female
- Enclosure Type: Steel
- Audio Support: No
- KVM Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 16
- Rack-Mountable: Yes
- KVM TFT: None
- Product Length: 180
- Maximum Cascaded Computers: 136
- Maximum Number of Computers: 16
- Maximum Analog Resolutions: 1920 x 1440
- Maximum Number of Users: 1
- OSD & Hotkey Support: Yes
- Carton Quantity: 3
- Shipping (Package) Weight: 6.5 lb [2.94 kg]
- Product Width: 436
- Ports: 16 PC ports (HDDDB15 Male, 2x 6 Pin MiniDIN Female), 1 Console port (HDDDB15 Female, 2x 6 Pin MiniDIN Female), 1 Feature Expansion port (8 pin MiniDIN Female)
 - PC Selection: OSD Menu, Keyboard hot-key, Front panel button
 - Video Bandwidth: 200 MHz
 - Enclosure: Metal
 - Certifications: FCC Part 15 Class A, CE Mark, VCCI