

## 2 User 8 Port PS/2 KVM Switch Modules for 1UCABCONS/17/19

StarTech ID: CAB832DS



This dual user shared 8 Port KVM Switch Module is designed for use with StarTech.com's DuraView 1UCABCONS series (1UCABCONS, 1UCABCONS17, 1UCABCONS19) 1U Folding Rackmount LCD Consoles.

Adding versatility and convenience, this module offers two user console access, allowing multiple computers to be controlled from two consoles/control points as opposed to just one.

**Note:** This product is designed to work in a "cascaded" configuration as a master KVM with non dual-user slave units attached.

## Features

- Ability to assign computers with unique and meaningful names
- Cascade configuration expands system ability allowing user to select computers connected to master and cascaded slave
- LCD panel on 1UCABCONS supports VGA resolution up to 1024x768 without any degradation
- Password security locks computer(s) from unauthorized access
- Supports both PS/2 and serial mice, including the Microsoft Intellimouse (Pro) and scroll mice

## Technical Specifications

- Color: Black
- Connector Types: 1 - 8 DIN Female
- Connector Types: 20 - 6 DIN Female
- Connector Types: 2 - High Density DB15 Female
- Connector Types: 8 - High Density DB15 Male
- Connector Types: 1 - Centronics 50 Female
- Enclosure Type: Steel
- Audio Support: No
- KVM Cascadable: Yes
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: PS/2
- KVM IP Control: No
- Number of KVM Ports: 8
- Rack-Mountable: Yes
- KVM TFT: None
- Product Length: 7.09 in [180 mm]
- Maximum Cable Length: 1200 in [3048 cm]
- Maximum Number of Computers: 8
- Maximum Analog Resolutions: 1920 x 1440 pixels
- Maximum Number of Users: 2
- Carton Quantity: 5
- U Height: 1
- Shipping (Package) Weight: 5.04 lb [2.28 kg]
- Operating System(s): OS independent, transparent to all applications
- System Configuration: Plug and play
- Ports: 10 x DB15, 20 x PS/2

- Video: 1920x1440, DDC2B compatible
- Hot Plug: Yes, keyboard and mouse
- Includes: 2 x PS/2 Female to DB9 Female serial mice adapters
  - 2 x Cabinet 19" 1U Rack mount brackets with screws
- Auto-Scan Rates: 3, 8, 15 and 30 seconds
- Max Cable Length: 100ft (30m) at console, 100ft at PC ports
- Cert: FCC (Part 15)