

2 Port CardBus Laptop USB 2.0 PC Card Adapter

StarTech ID: CBUSB22



This 2 Port CardBus USB 2.0 Adapter adds two USB 2.0 ports to your laptop or desktop computer, with support for full high-speed USB data transfer rates of up to 480 Mbps.

The USB 2.0 CardBus adapter offers backward compatibility with USB 1.1 devices, ensuring seamless operation with older USB peripherals and supports hot-swappable operation to provide hassle-free peripheral connections without having to reboot the computer.

Designed to provide a permanent USB 2.0 solution, the CardBus adapter is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

Applications and Solutions

- Digital cameras
- DVD drives
- External CDR/RWs

- Flash card readers/writers
- Joysticks
- Mice and keyboards
- MP3 players/iPods
- PDAs
- Portable hard drives
- Printers
- Scanners
- Webcams

Features

- 40 times faster than USB 1.1
- Backward compatible with USB version 1.1
- Compliant with Universal Serial Bus Specification Revision 2.0
- Connect up to 127 devices by cascading multiple hubs
- Easy plug and play installation
- OS Support: Windows 98SE/ME/ 2000/XP/Vista, and MAC SO 10.2 and up, and Linux

Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: CardBus
- Chipset ID: VIA - VT6212
- Connector Types: 2 - USB A Female
- Product Height: 0.59 in [1.5 cm]
- Product Length: 4.53 in [11.5 cm]
- Number of Ports: 2
- Operating Temperature: 0°C to 85°C (32°F to 185°F)
- Carton Quantity: 50
- Storage Temperature: -55°C to 125°C (-67°F to 257°F)
- Shipping (Package) Weight: 0.31 lb [0.14 kg]
- Product Weight: 0.11 lb [0.05 kg]
- Microsoft WHQL Certified: Yes
- Product Width: 2.17 in [5.5 cm]
- Minimum Processor Requirements: Intel Pentium Pro, Pentium III, P4, or better.
- Socket Type: 32 Bit CardBus Compatible PCMCIA Type II slot
- OS Compatibility: Windows 98SE/ME/2000/XP/Server 2003/Vista

Mac OS X (10.2.X)

Linux

