

165 foot (50 meter) Active DVI Extension Cable

StarTech ID: *DVIAEXT50*



Extend the range of your DVI-enabled displays without losing signal quality! StarTech.com's Active DVI extension cables deliver crystal-clear digital images instantly – with a sharper, stronger signal than standard VGA monitor cables. Even over longer distances the quality of your digital images is preserved. Backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Conference Rooms
- Educational Institutions
- Hospitals
- Transportation Industry

Features

- Compliant with the DVI 1.0 standard
- High 1600 x 1200 pixel UXGA resolution
- High speed digital transmission up to 1.25 Gbits/sec
- Immune to EMI and RFI with crystal-clear signal quality across long distances
- Supports hot plugging of DVI display devices for quick setup

Technical Specifications

- Connector A: 1 - DVI-D Single Link Male
- Connector B: 1 - DVI-D Single Link Male
- Color: Orange
- Product Length: 1968.5 in [50000 mm]
- Maximum Analog Resolutions: 1280 x 1024
- Carton Quantity: 1
- Shipping (Package) Weight: 8.95 lb [4.05 kg]
- Length: 165 feet (50 meters)
- Cable Type: DVI-D (True Digital Video)
- Connectors:
 - Connector A: 18-pin DVI-D (Male)
 - Connector B: 18-pin DVI-D (Male)
- Fiber: H-PCF Graded multi-mode fiber
- Industry Standards: HDCP compliant
- Maximum Resolution: 1600 x 1200 pixels (UXGA)
- Note that this product is not intended for use with widescreen displays.