

**HDTV DVI Repeater/Extender HDCP compliant**

*StarTech ID: DVIHDCPEXT*



Don't be held back by DVI cable limitations - now, you can extend your DVI connection by 12m (24m total extension), while enjoying an astounding 1080i or 1600x1200(UXGA)resolution.

## Features

- Cascadable up to three levels to achieve maximum transmission distance of 72 metres
- Corrects signal error and extends DVI transmission by 12 meters without degradation
- DDC pass through ensures proper recognition of the connected display
- HDCP 1.1 compliant and backwards compliant with HDCP 1.0
- Plug and Play, easy to install

## Technical Specifications

- Color: Black
- Connector Types: 1 - DVI-D Dual Link Female
- Enclosure Type: Aluminum
- Product Height: 1.18 in [30 mm]
- LED Indicators: 1 - Power LED (red)
- Product Length: 4.13 in [105 mm]
- Maximum Analog Resolutions: 1080p (HDTV) / 1600x1200 (PC)
- Number of Ports: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 2000mA
- Power Adapter - DC Voltage: DC 5V
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Shipping (Package) Weight: 1.13 lb [0.51 kg]
- Product Weight: 0 lb [0 kg]
- Product Width: 2.99 in [76 mm]
- Input Connector: DVI-D dual link female connector
- Output Connector: DVI-D dual link female connector