

## 95mm Socket T 775 CPU Cooler Fan with Heatsink

StarTech ID: FAN775E



This Socket T/775 cooler is designed specifically for the Intel Socket 775 (Socket T) range of processors, including Intel Core 2 Duo and Intel Core 2 Quad, Core 2 Duo Extreme CPUs.

The CPU cooler features a large aluminum heatsink that maximizes dissipation of the heat around the CPU, as well a low-noise 95mm fan that provides up to 50 CFM of air circulation, helping to keep the CPU cooler for optimized performance.

The Socket 775/T cooler/fan offers simple installation, providing tool-less clips for easy connection to the motherboard.

A dependable, high quality CPU cooling solution, the Socket 775/Socket T CPU cooler is backed by StarTech.com's 1-year warranty.

### Applications and Solutions

- Compatible with following Intel Socket T/775 Core 2 Processors:

Core 2 Quad Up to Q6600

Core 2 Extreme Up to QX6700

Core 2 Duo (All Models)

- Compatible with following Intel Socket T/775 Dual Core & Pentium Processors:

Pentium Extreme Edition: 840-965

Pentium D: 805-840 / 915-960

Pentium 4 Extreme Edition Up to 3.73 GHz

Pentium 4: 505-570J / 620-672

- Keep your CPU running smooth and efficient without the worries of overheating.

## Features

- An efficient solution with a special fin design to ventilate and help cool your CPU
- Large aluminum heatsink provides efficient heat dissipation
- Tool-less clip for quick and easy installation.

## Technical Specifications

- Warranty: 1 Year warranty
- Air Flow Rate: 49.37
- Color: Black
- Product Height: 2.67 in [67.7 mm]
- Input Voltage: 12 DC
- Product Length: 3.74 in [95 mm]
- Noise Level: <22.2 dBa
- Carton Quantity: 20
- RoHS Availability: Yes
- RPM: Rated Speed : 2600 ±10% RPM
- RPM: Rated Speed (Add Heatsink to fan): 2800 ±10% RPM
- Shipping (Package) Weight: 0.97 lb [0.44 kg]
- Product Weight: 13.2 oz [374 g]
- Product Width: 3.74 in [95 mm]
- General Specifications: Supports Intel Core 2 Duo Processor and Intel Core 2 Quad Processor
- Heatsink Material : Aluminum
- Fan Dimension: 95 x 95 x 25 mm
- Bearing Type : 95mm Ever Lubricate bearing
- Connector: 3 pin internal connector

