

4 Port PCI Express 1394a FireWire Adapter Card - 3 External 1 Internal

StarTech ID: PEX13943



This 4 Port PCI Express 1394a FireWire Adapter Card turns a PCI Express slot into three external and one internal 1394a ports, allowing you to connect portable drives, digital camcorders and more to your desktop computer.

The adapter card supports hot-swapping, so you'll be able to plug, unplug, and swap your FireWire peripherals with ease, without having to power down the computer. It also includes a low profile bracket that makes the adapter card suitable for installation in slimline or small/micro form factor systems.

Applications and Solutions

- Digital camcorders
- Digital cameras
- DVD drives
- External CDR-CDRW drives
- iPods/MP3 players
- Portable hard drives
- Printers
- Scanners

Features

- Compliant with IEEE 1394 OpenHCI Specifications V1.0 and V1.1
- Compliant with PCI Express Specification 1.0a
- High speed data transfer rates of up to 400 Mbits/sec.
- Hot swap capabilities allows you to connect or disconnect devices without turning off your computer

Technical Specifications

- Bus Type: PCI Express
- External Ports: 3 - FireWire 6-pin Female
- Internal Ports: 1 - FireWire 6-pin Female
- Number of Ports: 4
- Carton Quantity: 50
- Industry Standards: IEEE 1394/1394a
- Industry Standards: OHCI
- Shipping (Package) Weight: 0.24 lb [0.11 kg]
- Microsoft WHQL Certified: Yes
- Bus Type: PCI Express x1
- OS Support: Windows 2000/XP/2003/Vista, MAC OS X and up
- Chipset: NEC D72874
- **Note:** If internal port is used, one external port will be disabled. Only three ports will function simultaneously.