


10 ft 24V to Hosiden+USB B PoweredUSB Cable

StarTech ID: PUSBDYB24V10



Providing both USB data and USB device power through a single cable, Powered USB technology is emerging as the industry standard in a broad range of environments including retail POS, industrial, security and medical, based on true plug-and-play connectivity.

StarTech.com's versatile line of powered USB cables provides the high quality design and construction needed to usher in a new generation of USB connectivity, providing superb grounding and protection for all components as well as protection against the normal wear and tear that can result from repeated insertions and removals.

This 24v to Hosiden + USB B Powered USB cable is backed by lifetime warranty to ensure long-lasting durability and optimum performance.

Features

- Compatible with USB 1.1/2.0 standards and Powered USB peripheral devices
- Eliminates the use of a power adapter
- Plug and Play
- Power your peripheral and provide USB connectivity with a single cable.
- Reduces clutter and frees up space

Technical Specifications

- Color: Beige
- Cable Length: 10 ft [3.05 m]
- Connector A: 1 - 8 pin USB PlusPower (24 V) Male
- Connector B: 1 - USB B Male
- Connector B: 1 - 3 pin Power mini-DIN Male
- Type and Rate: USB 2.0 - 480 Mbit/s
- Carton Quantity: 50
- Shipping (Package) Weight: 0.64 lb [0.29 kg]