

## 1U 19in Steel Vertical Rack and Wall Mountable Server Rack

StarTech ID: RK119WALLV



This 1U 19in Wallmount Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 1U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace.

Perfect for SoHo (small office, home office) environments, the wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design and is backed by StarTech.com's Lifetime Warranty.

Need more storage space? StarTech.com also offers a [2U 19in Wallmount Bracket](#), a [3U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

### Applications and Solutions

- Ideal for small and medium businesses needing rack solutions
- Mount KVM switches or workstations under a desk or work bench to free up work spac
- Mount servers and telecommunication equipment flush against the wall

## Features

- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack.
- Compatible with most 19" rack mountable equipment
- Constructed to meet the EIA-310 19" rack standards
- Equipment can be vertically wall mounted, or horizontally under a desk
- Made from solid steel for durability
- Wall mounting holes are 16" center to center for greater stability, and mounting into standard wall studs.

## Technical Specifications

- Warranty: Lifetime warranty
- External Height : 5.94 in [151 mm]
- Carton Quantity: 1
- Shipping (Package) Weight: 2.03 lb [0.92 kg]
- Color: Black
- Frame Type: : Steel
- External Width : 19.84 in [504 mm]
- External Depth : 2.36 in [60 mm]
- Internal Width: 17.72 in [450 mm]
- U Height: 1
- Product Weight: 23.3 oz [660 g]

