

## Black 4U Steel Rackmount Server Case

StarTech ID: RMC4000I



This rugged 4U Rackmount Server Case features a 1mm steel chassis that lets you keep your rackmounted industrial PCs or servers protected from dust and damage while allowing superior airflow to ensure reliable, stable operation even in harsh industrial environments.

Providing a reliable 12cm front fan and a lockable front panel door, this 4U Server case can accommodate up to two additional 60mm fans in the rear of the chassis, providing not only a solid platform from which to build your server or rackmount PC, but also a scalable cooling solution that ensures you can maintain necessary operating temperatures in any environment.

### Applications and Solutions

- Industrial automation control PCs
- Industrial servers
- Industrial workstation PCs

## Features

- 120mm front fan with air filter provides plenty of clean air circulation. Can accommodate up to two additional 60mm fans in rear.
- Adjustable I/O card holders prevent cards from becoming unseated in their slots
- Full front panel lockable protective door
- Rugged 1mm SECC steel construction
- Temperature and fan failure LEDs warn of possible impending system failure

## Technical Specifications

- Warranty: 1 Year warranty
- Number of external 3.5 inch bays: 1
- Number of internal 3.5 inch bays: 1
- Number of external 5.25 inch bays: 3
- Color: Black
- Number of expansion slots: 7
- Optional Fan Mounts: 2 - 60 mm
- Product Height: 6.97 in [177 mm]
- LED Indicators: 1 - Power
- LED Indicators: 1 - Hard drive activity
- LED Indicators: 1 - Fan failure warning
- LED Indicators: 1 - Temperature warning
- Product Length: 18.5 in [470 mm]
- Motherboard Compatibility: ATX
- Fans: 1 - 120 mm
- Carton Quantity: 1
- Shipping (Package) Weight: 26.56 lb [12.02 kg]
- Product Weight: 37.57 lb [17 kg]
- Product Width: 19.02 in [483 mm]
- Fan Filter: Washable foam
- Case Entry: 2 screws
- Front Door: Full Front Lockable

