

5.25in Silver eSATA USB 2.0 to SATA Optical Drive Enclosure

StarTech ID: SAT5210U2E



This versatile drive enclosure offers a cost-effective way to turn any SATA II 3.5in hard drive (up to 1.5TB) or 5.25in optical drive (Blu-ray DVDRW, CD-ROM, CD-RW, DVD-ROM, DVD-RW), into an external solution.

The drive enclosure can be connected to a host computer through either USB 2.0 or eSATA, and supports the full capability of both interfaces (maximum data transfer capability up to 3 Gbps with eSATA, up to 480 Mbps through USB 2.0).

To help ensure dependable drive operation, the enclosure provides a sturdy yet attractive aluminum casing and a 40mm fan to help keep the installed hard drive or optical drive cool.

Drives can be installed in the enclosure in minutes, and includes the added convenience of a stereo headphone jack for computer-free CD playback.

Applications and Solutions

- Add external DVD/CD burning capability to notebooks and desktops with USB or eSATA connectivity.
- Turn any internal SATA I/II drive into an external DVD/CD drive or storage.

Features

- Allows 3.5" SATA I/II (SATA 150/300) Hard Drives (including 1.5 terabyte) and 5.25" SATA Optical Drive in one enclosure.
- Aluminum casing and 40mm fan for maximum heat dissipation
- Equipped with USB 2.0 and eSATA interfaces for maximum data transfer, and versatility
- Full plug and play support through USB 2.0 interface
- Quick and easy installation
- Stereo headphone jack for computer free CD playback

Technical Specifications

- Warranty: 1 Year warranty
 - Color: Silver
 - Enclosure Type: Aluminum
 - Product Height: 2.28 in [58 mm]
 - LED Indicators: 1 - Power LED: Green
 - Product Length: 10.2 in [259 mm]
 - Fans: 1 - 40 mm
 - Power Adapter Included: Yes
 - Power Adapter - Amperage: 2A
 - Power Adapter - DC Voltage: 12VDC
 - Center Tip Polarity: Positive
 - Carton Quantity: 10
 - Shipping (Package) Weight: 3.45 lb [1.56 kg]
 - Product Weight: 32.83 oz [930 g]
 - Product Width: 6.54 in [166 mm]
 - Connectors:
 - Internal Drive: 1x SATA Data 7 Pin Female
 - General Specifications: 1x SATA Power 15 Pin Female
 - Host: 1x eSATA Data Male
 - General Specifications: 1x USB B Male
 - Maximum Data Transfer Rate: Up to 3 Gbps with eSATA, 480 Mbps with USB 2.0
 - Supported Optical Drive: SATA I/II (SATA150 and SATA300) CD-ROM/RW, DVD ROM/RW, Blu-Ray DVD ROM/Writer
- Tested Blu-Ray DVD Drives:
Lite-On LH-2B1S

LG GGW-H20LPanasonic SW-5583

- Supported Hard Drive: 3.5" SATA I/II (SATA150 and SATA300) Hard Drive up-to 1.5TB
- OS Compatibility: Windows 98SE/ ME/ 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), Mac OS 9x and up, and Linux

