

2 Port Wall Mount VGA Video Splitter

StarTech ID: ST122W



This 2 Port wall-mountable VGA Video Splitter offers outstanding quality and distance, allowing you to deliver high resolution VGA video from a single video source to up to two monitors simultaneously.

The wall-mountable multi-display VGA video splitter is very simple to install, allowing you to locate screens up to 200ft away from the VGA video source, supporting a maximum VGA video bandwidth of up to 250MHz while delivering display resolutions up to 1600 x 1200.

The video splitter provides versatile installation options, with top-side connection ports as well as the option to mount the splitter on a wall, making it easy to position the VGA splitter as needed.

The VGA video splitter offers a scalable video splitting solution, allowing you to cascade the VGA signal using two additional splitters for broadcast from a single VGA source to up to 8 VGA monitors.

Typical applications of this product would include digital signage, retail and tradeshow environments, educational and government facilities, or corporate displays where high quality, multi-monitor VGA video is required.

StarTech.com's 2 Port wall-mountable VGA Video Splitter is backed by our 1-year warranty and includes free lifetime technical support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- Cascadable up to 3 levels to provide up to eight video signals
- Compact design with convenient topside connection, lays flat or mounts on the wall
- Supports Distances up to 200ft
- Supports resolutions up to 1600x1200.

Technical Specifications

- Color: Silver
- Connector Types: 2 - DB15 High Density Female
- Connector Types: 1 - DB15 High Density Male
- Enclosure Type: Plastic
- Product Height: 0.22 in [5.5 mm]
- Product Length: 0.34 in [8.75 mm]
- Maximum Analog Resolutions: 1600 x 1200
- Number of Ports: 2
- Operating Temperature: 0 ~ 50 degree C
- Power Adapter Included: Yes
- Power Adapter - Amperage: 300mA
- Power Adapter - DC Voltage: 9V DC
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Storage Temperature: -20 ~ 60 degree C
- Shipping (Package) Weight: 0.88 lb [0.4 kg]
- Product Width: 0.06 in [1.5 mm]
- VGA Bandwidth: 250 MHz
- Max Distance: Up to 65m / 200ft