

4 Port HDMI Audio / Video Splitter

StarTech ID: ST124HDMI



This 4-Port HDMI video splitter lets you share a single HDMI OUT port with up to four HDMI-capable displays/receivers, with no loss of image quality.

Supporting true HD video resolutions up to 1080p, the HDMI splitter also acts as an HDMI video distribution amplifier/signal amplifier, allowing you to locate your HDMI-capable displays up to 50ft (15m) away from the HDMI source.

A perfect addition to virtually any application requiring the high quality video delivered by HDMI devices, the HDMI video splitter is easy to install and provides flawless, distortion-free digital video.

The 4-port HDMI video splitter offers dependable operation and is backed by StarTech.com's 1-year warranty and free lifetime technical support.

Applications and Solutions

- Connect HDMI enabled projectors, monitors, plasma screens, commercial billboards, and wall display systems
- Ideal for classroom, corporate, healthcare, professional A/V, control centres, conference halls, and retail environments.

Features

- Built-in EDID simulator and HDCP keyset allows each output to work independently when connecting to a HDMI display.
- Can be cascaded up to 3 layers
- HDMI 1.1 and HDCP 1.1 Compliant
- Splits a HDMI source up to 4 outputs without signal loss.
- Supports a wide range of PC and HDTV resolutions-from VGA to UXGA and 480p to 1080p.

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Enclosure Type: Steel
- Carton Quantity: 15
- Shipping (Package) Weight: 1.68 lb [0.76 kg]
- Frequency bandwidth: 1.65Gbps(single link)
- Resolutions Supported: HDTV Resolution 480i to 1080p

PC Resolution VGA to UXGA

- Input Ports: 1 x HDMI Female
- Output Ports: 4 x HDMI Female
- Number of Ports: 4
- Operating temperature range: 0 - 70 C
- Operating humidity range: 30 to 80% RH
- Power Adapter Included: Yes
- Input Voltage: Universal 115 ~ 230 AC
- Power Adapter - DC Voltage: 5 DC
- Power Adapter - Amperage: 2.6 Amp
- Center Tip Polarity: Positive

