

4 Port VGA Video Splitter - 250 MHz

StarTech ID: ST124L



This VGA Video Splitter / Distribution Amplifier allows a computer to display VGA video on four monitors simultaneously - the perfect solution for classrooms, tradeshows, or in-store displays where high quality video on several monitors is required.

Providing support for up to 250 MHz of video bandwidth, the four port VGA Video Splitter provides brilliant 1920x1440 resolution and features a built-in booster circuit that allows you to locate VGA displays up to 210 ft away from the signal source. Plus, the video splitter provides easy plug and play installation that lets you take your show anywhere and set up in seconds!

This VGA Video Splitter / Distribution Amplifier is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- 250 MHz bandwidth provides brilliant resolutions up to 1920 x 1440 pixels
- Compatible with VGA, SVGA and Multisync monitors
- Daisy chainable up to three levels.

Technical Specifications

- Color: Black
- Product Height: 1.02 in [25.91 mm]
- Product Length: 2.56 in [65.02 mm]
- Number of Ports: 4
- Carton Quantity: 10
- Shipping (Package) Weight: 2.14 lb [0.97 kg]
- Product Weight: 7.8 oz [221 g]
- Product Width: 5.16 in [13.11 cm]
- Video Input: 1 x HD-15 VGA Male Connectors
- Video Output: 4 x HD-15 VGA Female Connectors
- Video Bandwidth: 250 MHz
- Maximum Video Resolution: 1920 x 1440
- Maximum Cable Distance: 210 feet (65m)
- Power Adapter: DC 9V 500mA
- EDID Support: No