

4 Port VGA Video Splitter - Wall Mountable

StarTech ID: ST124W



This 4 Port wall-mountable VGA Video Splitter offers outstanding quality and distance, allowing you to deliver high resolution VGA video from a single video source to up to four monitors simultaneously.

The wall-mountable multi-display VGA video splitter is very simple to install, allowing you to locate screens up to 200ft away from the VGA video source, supporting a maximum VGA video bandwidth of up to 250MHz while delivering display resolutions up to 1600x1200.

The video splitter provides versatile installation options, with top-side connection ports as well as the option to mount the splitter on a wall, making it easy to position the VGA splitter as needed.

The VGA video splitter offers a scalable video splitting solution, allowing you to cascade the VGA signal using additional splitters for broadcast from a single VGA source to up to 64 VGA monitors.

Typical applications of this product would include digital signage, retail and tradeshow environments, educational and government facilities, or corporate displays where high quality, multi-monitor VGA video is required.

StarTech.com's 4 Port wall-mountable VGA Video Splitter is backed by our 1-year warranty and includes free lifetime technical support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- Cascadable up to 3 levels and provides up to 64 video signals
- Compact design with convenient topside connection, lays flat or mounts on the wall
- Supports distances up to 65m / 200ft
- Supports resolutions up to 1600 x 1200 resolution

Technical Specifications

- Color: Silver
- Connector Types: 2 - DB15 High Density Female
- Connector Types: 1 - DB15 High Density Male
- Enclosure Type: Plastic
- Maximum Analog Resolutions: 1600 x 1200
- Number of Ports: 4
- Operating Temperature: 0 ~ 50 degree C
- Power Adapter Included: Yes
- Power Adapter - Amperage: 300mA
- Power Adapter - DC Voltage: 9V DC
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Storage Temperature: -20 ~ 60 degree C
- Shipping (Package) Weight: 1.1 lb [0.5 kg]
- Max Distance: 65m / 200ft
- VGA Bandwidth: 250 MHz