

4 Port StarView DVI and VGA Dual Display USB KVM Switch with Audio

StarTech ID: SV431DDUSB



StarTech.com's 4 port DVI/VGA USB KVM Switch with Audio is a complete USB dual display multimedia switching solution.

With support for high-resolution DVI and VGA video interfaces, the dual display KVM switch provides one VGA analog and one DVI-I port, as well as audio and USB switching - integrating a 2 port USB hub and audio/mic channels that can be switched either simultaneously or independently from the PC, to provide the multimedia flexibility you need.

Plus, the DVI/VGA USB KVM Switch features a rugged metal chassis with a compact form factor that won't eat up your valuable desk space.

Applications and Solutions

- Great solution for environments using desktops, workstations and servers where both VGA and DVI digital are required
- Ideal for financial/banking industries, graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution dual display units are needed
- Ideal for multimedia computer systems supporting Dual Head video cards
- Suitable for use in environments with electromagnetic interference and wherever a sturdy protective metal case is needed

Features

- Direct channel selection and operation using front-panel push button and keyboard hotkeys
- DVI-I Single Link interface technology supports digital and analog video signal transmission
- HDCP compliant for digital contents protection
- Metal enclosure for best shielding and protection
- Status LED display for easy port status monitoring
- Support DDC2B emulation, which allows the display adapter to recognize and auto configure the display resolution to match the display capabilities
- Supports Dual Monitor/Flat Panel Displays [1 x DVI + 1 x VGA]
- USB style keyboard and mouse, plus two other USB peripherals can be shared between up to two computers

Technical Specifications

- Color: Black
- Enclosure Type: Steel
- Product Height: 2.6 in [66 mm]
- Product Length: 9.96 in [253 mm]
- Maximum Number of Computers: 4
- Maximum Analog Resolutions: 2048 x 1536 (analog) / 1920 x 1200 (digital)
- Maximum Number of Users: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 1.7
- Power Adapter - DC Voltage: 9V
- Center Tip Polarity: Positive
- Carton Quantity: 6
- Shipping (Package) Weight: 3.71 lb [1.68 kg]
- Product Weight: 0.04 oz [1.15 g]
- Product Width: 3.94 in [100 mm]
- Console Port Connectors: 1 x DVI-I Female
 - 1 x VGA Female
 - 4 x USB Type A
 - 2 x 3.5mm for Mic/Audio
- PC Port Connectors: 4 x DVI-I Female
 - 4 x VGA Female
 - 4 x USB type B
 - 8 x 3.5mm for Mic/Audio