

USB KVM Switch 4 Port with Audio Starview

StarTech ID: SV431USBAE



This Rack Mountable USB KVM Switch supports high resolution video applications (up to 1920x1440 pixels supported) and audio switching between connected computers, and provides an integrated USB 2.0 hub that lets the selected computer have access shared high speed USB peripherals.

Providing control of up to four computers from a single USB keyboard and mouse peripheral set, the switch features a sturdy all metal chassis and can be rackmounted in a server rack/cabinet using an optional [Rackmount Bracket kit](#) (SV431RACK) - minimizing clutter and saving space.

Applications and Solutions

- Control up to four computers, sharing a single keyboard, mouse, monitor and speakers.
- Integrated USB 2.0 hub allows you to share up to three USB peripherals between the four computers.

Features

- All metal chassis for long-term durability
- Audio switching with microphone and speaker connectivity
- Auto-scan function automatically selects computer sequentially
- Compatible with all USB supported Operating Systems
- Designed for high-resolution applications: up to 1920x1440 pixels supported
- Front panel push button computer selection
- Integrated USB 2.0 hub allows you to share up to three high-speed USB devices between computers

Technical Specifications

- Color: Black
- Enclosure Type: Steel
- Product Height: 1.75 in [44.5 mm]
- Audio Support: Yes
- KVM Cascadable: No
- Dual Display Support: No
- DVI Support: No
- Supported Platforms: USB
- KVM IP Control: No
- Number of KVM Ports: 4
- Rack-Mountable: Yes
- KVM TFT: None
- Product Length: 8.66 in [220 mm]
- Maximum Number of Computers: 4
- Maximum Analog Resolutions: 1920x1440
- Maximum Number of Users: 1
- Power Adapter Included: Yes
- Power Adapter - Amperage: 2.0
- Power Adapter - DC Voltage: 5
- Center Tip Polarity: Positive
- Carton Quantity: 6
- U Height: 1
- Shipping (Package) Weight: 3.67 lb [1.66 kg]
- Product Weight: 36.39 oz [1031 g]
- Product Width: 5.12 in [130 mm]
- Console Connectors: VGA HD-15 female (1)

- USB 2.0 hub Type A (4)
- 3.5mm Microphone (1)
- 3.5mm Speaker (1)
- PC Port Connectors (each): VGA HD-15 Male (1)
- USB Type B female (1)
- 3.5mm Microphone (1)
- 3.5mm Speaker (1)