

Remote User Station for Enterprise IP KVM Switch

StarTech ID: SV5CONS



This Remote User Station for Enterprise Series IP KVMs provides system administrator access to StarTech.com Enterprise series KVM solutions (i.e. SV1653DXI) located up to 1000 ft. (300m) away - allowing convenient control of two separate KVM solutions without the need of a complete work station.

Applications and Solutions

- Allows a remote user to have local access to the KVM and attached servers.
- Control two enterprise series KVMs from one remote location up to 1000ft. away.

Features

- Compact design, with durable hardened metal casing
- Hot-key support
- LED indicator for KVM identification
- Supports a resolution of up to 1280 x 1024 @75, 1000ft. (300m) away
- Supports most standard USB keyboards and mice

Technical Specifications

- Color: Black
- Product Height: 0.94 in [24 mm]
- Product Length: 4.02 in [102 mm]
- Maximum Cable Length: 984 ft [300 m]
- Maximum Analog Resolutions: 1280 x 1024 @75Hz
- Power Adapter Included: Yes
- Power Adapter - Amperage: 3000mA
- Power Adapter - DC Voltage: 5V DC
- Center Tip Polarity: Positive
- Carton Quantity: 10
- Shipping (Package) Weight: 1.15 lb [0.52 kg]
- Product Weight: 6.71 oz [190 g]
- Product Width: 4.41 in [112 mm]
- Construction : Aluminum
- LED : Green – Port Indicator
- Connectors:
 - 1 x HDDB15 Female
 - 2 x USB Type A Female
 - 2 x RJ45 Female