

USBthere - 1 Port 330 Foot (100 Meter) Powered USB Extender

StarTech ID: USB201EXT



Boost the distance of your USB connection with the USBthere, a one-port powered USB extender from StarTech.com. You'll be able to place your high power USB devices up to 330 feet (100m) away from your computer, an incredible 20 times greater than normal USB length restrictions. The Local and Remote units connect using standard Cat 5e Ethernet Cable and there's no need to buy additional hubs, repeaters or software, you just plug in and go.

Perfect for USB video cameras, scanners, and POS equipment, the USBthere maintains the USB 1.1 standard with data transfer rates of up to 12 Mbits/sec. With the USBthere, extending the range of your USB devices has never been easier.

Applications and Solutions

- Ideal for use with remote digital recorders, security and surveillance equipment, POS devices, printers, scanners as well as any other USB peripheral

Features

- Allows users to make use of existing Ethernet infrastructure for extending USB devices
- Extends the range of one USB device up to 330 feet (100 meters) using standard Cat 5e Ethernet cables
- Comes complete with a 6 foot USB cable and an external power adapter
- Compliant with USB 1.1 specifications
- Data transfer rates of up to 12 Mbits/sec
- Easy installation and set up with no software required

Technical Specifications

- Warranty: 1 Year warranty
- Product Height: 1.34 in [34 mm]
- LED Indicators: 1 - Power
- LED Indicators: 1 - Host
- LED Indicators: 1 - Link
- Product Length: 4.21 in [107 mm]
- Number of Ports: 1
- Shipping (Package) Weight: 2.36 lb [1.07 kg]
- Product Weight: 10.59 oz [300 g]
- Product Width: 3.31 in [8.4 cm]
- Extension Distance: 330 ft (100 m)
- USB Compatibility: Supports USB 1.0 and USB 1.1 devices (multi-speed)
- Dimensions: 4.2 x 3.3 x 1.3 Inches (107 x 84 x 34 mm)
- Weight: 1.2 lbs (0.6 kg)
- Local Unit Connectors: Upstream: 1 x 4 pin USB (Type B)

Downstream: 1 x RJ-45

- Remote Unit Connectors: Upstream: 1 x RJ-45

Downstream: 2 x 6 pin USB (Type A)

- Total Shipping Weight: 2.4 lbs (0.8 kg)
- Color: Black
- USB Hub Support: Up to 4 hubs connected to the local unit
- Enclosure Type: Steel
- Maximum Cable Length: 328 ft [100 m]
- Operating Temperature: 4 to 40 °C

- Industry Standards: USB 1.1
- Data Transfer Rate: Up to 12 Mbits/sec
- Maximum power available to USB at the Remote Unit: 500 mA
- Input Voltage: 15V DC

