

## USB DVI VGA External Dual or Multi Monitor Video Adapter

StarTech ID: USB2DVIE



This USB to DVI/VGA Multi-Monitor External Video Adapter acts as an external video card for any USB 2.0 laptop or desktop computer. The external video adapter converts a USB 2.0 port into a DVI-I port - providing high quality dual display or multi-monitor capability that allows you to mirror or extend the desktop shown on the existing display as needed.

For an even more versatile multi display configuration, up to five USB to DVI/VGA video adapters can be connected to the same computer simultaneously, allowing for a total of five USB connected DVI monitors to display video from a single computer.

The USB to DVI/VGA External Multi Monitor Video Adapter can also be connected to VGA monitors using the included DVI to VGA adapter, and can be connected to an HDMI display using a [DVI to HDMI Adapter](#) (HDMIDVIFM - Not included).

### Applications and Solutions

- Excellent solution for notebooks enabling the connection of multiple adapters to multiple displays (up to six monitors, including notebook display).
- Run in extended mode where your desktop can span across multiple screens or mirror you image as if you were using a video splitter.
- Run multiple applications on different screens, check your email on one display and work on a document in the other.

## Features

- Acts as an external video card connected through USB 2.0
- Add a secondary display adapter and extend your desktop/notebook display without taking apart your computer to install a new video card
- No power adapter required and easy to install
- Supports resolutions up to 1600x1200 and 1680x1050(for widescreen / format displays) @ 32 bits

## Technical Specifications

- Built-in Memory: 16MB RAM
- Maximum Displays: Connect up to five adapters on one PC.
- OS Support: Windows 2000/XP, Vista 32/64 bit.
- Video Signal: DVI-D and DVI-A (digital and analog)
- Color: Black
- Connector Types: 1 - DVI-I Single Link Female
- Connector Types: 1 - USB Mini B 5 pin Female
- Product Height: 0.93 in [23.5 mm]
- Product Length: 3.54 in [90 mm]
- Carton Quantity: 20
- Shipping (Package) Weight: 0.71 lb [0.32 kg]
- Product Weight: 2.58 oz [73 g]
- Product Width: 1.89 in [48 mm]
- Supported Resolutions (Widescreen): 1920x1200 (16 bits)
  - 1920x1080 (16 bits)
  - 1680x1050 (16 and 32 bits)
  - 1440x900 (16 and 32 bits)
  - 1280x800 (16 and 32 bits)
  - 1280x768 (16 and 32 bits)
- Supported Resolutions (Standard): 1600x1200 (16 and 32 bits)
  - 1400x1050 (16 and 32 bits)
  - 1280x1024 (16 and 32 bits)
  - 1280x960 (16 and 32 bits)
  - 1152x864 (16 and 32 bits)
  - 1024x768 (16 and 32 bits)
  - 800x600 (16 and 32 bits)
- System Requirements: 1.2Ghz or higher CPU
  - 512MB RAM

- An available USB 2.0 Port
- 30MB of hard drive space