

## USB VGA External Dual or Multi Monitor Video Adapter - High Resolution

StarTech ID: USB2VGA2



The USB2VGA2 USB VGA Adapter turns a USB 2.0 port into a VGA port, with support for 32-bit graphics (up to 1600 x 1200 resolution), to deliver a high quality dual display or multi-monitor configuration that can be used in a variety of laptop or desktop applications.

For even more versatility, up to five USB to VGA External Video adapters can be used simultaneously, providing a simple and scalable solution for extending or mirroring an existing desktop or laptop display onto multiple monitors - a cost-effective solution that saves the hassle of installing a conventional video card.

### Applications and Solutions

- A cost-effective external graphics adapter for laptop applications
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Extend your desktop across multiple monitors and run spreadsheets or browse the internet with your additional displays

## Features

- Broad operating system support: Windows 2000 SP4, Windows XP SP2 (32bit/64bit) and Windows Vista (32bit/64bit)
- No power adapter required, easy installation
- Supports resolutions up to 1600 x 1200 (32-bit), 1920 x 1200 (16-bit)

## Technical Specifications

- Warranty: 1 Year warranty
- Supported Resolutions (Standard): 1600x1200 (16 and 32 bits)
  - 1400x1050 (16 and 32 bits)
  - 1280x1024 (16 and 32 bits)
  - 1280x960 (16 and 32 bits)
  - 1152x864 (16 and 32 bits)
  - 1024x768 (16 and 32 bits)
  - 800x600 (16 and 32 bits)
- Supported Resolutions (Widescreen): 1920x1200 (16 bits)
  - 1920x1080 (16 bits)
  - 1680x1050 (16 and 32 bits)
  - 1440x900 (16 and 32 bits)
  - 1280x800 (16 and 32 bits)
  - 1280x768 (16 and 32 bits)
- Number of Displays: Install up to five additional displays. One adapter is required for each display.
- Connector Types: 1 - USB A Male
- Connector Types: 1 - DB15 High Density Female
- Carton Quantity: 20
- Shipping (Package) Weight: 0.64 lb [0.29 kg]
- OS Compatibility: Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit)

