

USB VGA Mini External Video Adapter Card

StarTech ID: USB2VGAE



This USB VGA mini External Video Card turns an available USB 2.0 port into a VGA port - providing high quality dual display capability that can be used in a variety of laptop or desktop applications.

Simply connect the adapter to a host computer through USB 2.0, then connect a VGA monitor to the port it provides.

The video adapter is a cost-effective external VGA video card for Windows CE 5.0 devices, as well as for Windows 2000, XP and Vista(tm) - a great option for viewing content from handheld/mobile devices or from a desktop/laptop computer on an added display.

A convenient and portable external video solution, the adapter is very compactly constructed. It features a lightweight and portable design that takes up very little space in a laptop bag or when connected to a computer, making it a practical solution for mobile applications.

Applications and Solutions

- Add a second monitor to your computer without the hassle of upgrading to a new video card avoiding technical or complicated issues related to running two video cards.
- Custom Applications: Use USB2VGAE with Windows CE 5.0 for custom or embedded applications

- In the office: View large or multiple spreadsheets across two screens.
- On the road: Since USB2VGAE is lightweight and portable it is an excellent solution for notebook PC's and easily having the ability to connect to a secondary display.

Features

- Add a secondary display adapter and extend your desktop display
- No power adapter required and easy to install
- Supports resolutions up to 1280x1024
- Supports Windows 2000/XP/Vista (Vista 32/64-bit) and Windows CE 5.0
- Works with desktop and laptop computers

Technical Specifications

- Warranty: 1 Year warranty
- System Requirements: One available USB 2.0 port
- Maximum Displays Supported: 1
- Supported Resolutions: 1280x1024 (16 and 32 bits)
 - 1024x768 (16 and 32 bits)
 - 800x600 (16 and 32 bits)
 - 640x480 (16 and 32 bits)
- Color: Gray
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 1 - USB A Male
- Product Height: 0.75 in [19 mm]
- Product Length: 3 in [76.2 mm]
- Carton Quantity: 20
- Shipping (Package) Weight: 0.27 lb [0.12 kg]
- Product Weight: 3.35 oz [95 g]
- Product Width: 1.75 in [44.5 mm]
- OS Compatibility: Windows 2000/ XP(32/64bit)/ Vista(32/64bit)/ 7(32/64bit), and Windows CE 5.0

