

4-in-1 USB VGA Adapter and Docking Station

StarTech ID: USBVGADOCK



This USB to VGA converter/adapter offers the combined functionality of a 4-in-1 docking station by converting a single USB 2.0 port into multiple connection ports, including a VGA Port, 10/100 RJ45 network port, dual (3.5mm phono) audio ports and four additional USB 2.0 ports.

With support for impressive 1600x1200 (32-bit) resolution for connected VGA Monitors, the 4-in-1 VGA dock helps to save time when swapping peripherals from one computer to another.

The USB VGA Adapter/Docking station offers a definite time-saving solution. Now, instead of disconnecting devices like speakers and USB peripherals (scanners, printers, webcams etc.) in order to re-connect them to another computer, all that is required is to remove the USB to VGA converter USB 2.0 connection to the computer, and insert it into an available USB 2.0 port on the secondary computer.

Applications and Solutions

- Perfect for any notebook user who wants a portable and desktop solution. Connect DB15, USB, Ethernet and Audio devices to your system

Features

- Acts as a USB 2.0 hub allowing you to connect a keyboard, mouse, printer, audio devices, and more
- Connect to an external monitor, with resolutions up to 1600x1200
- Provides greater flexibility for using your notebook as a desktop

Technical Specifications

- Color: Black
- Product Height: 0.75 in [19.1 mm]
- Product Length: 7.99 in [203 mm]
- Number of Ports: 4
- Power Adapter Included: Yes
- Power Adapter - Amperage: 3
- Power Adapter - DC Voltage: 5
- Center Tip Polarity: Positive
- Carton Quantity: 20
- Shipping (Package) Weight: 1.55 lb [0.7 kg]
- Product Width: 2.75 in [69.8 mm]
- LAN Speed: 10/100
- USB Transfer Rate: USB 2.0, supports up to 480 Mbps
- Maximum Resolution: 1600x1200 @ 32 bits and 1920 x 1200 @ 16 bits
- OS Support: Windows 2000, XP, and Vista (32-bit only)
- Connector Types: 4 - USB A Female
- Connector Types: 1 - USB Mini B 5 pin Female
- Connector Types: 1 - DB15 High Density Female
- Connector Types: 1 - RJ45 Female
- Connector Types: 2 - Phono 3.5 mm Female