

4 Port High Resolution VGA Video Switch with Remote

StarTech ID: VS415RVGA



This 4 port VGA Video Switch allows you to select between four separate VGA video signals for output to a single monitor or projector up to 65m (213ft) away from the video source.

A perfect solution for situations where VGA input ports are at a premium, the 4 port VGA Video Switch eliminates the hassle of having to swap out connections to your display, and allows you to select your video source at the push of a front panel pushbutton or by using the included remote control.

Applications and Solutions

- Excellent solution for connecting and switching between multiple PC's to one display.
- Great for use in presentations, tradeshows, conferences, retail, and entertainment applications.

Features

- Connect to your display at a maximum distance of 65 meters
- Solid construction in a metal enclosure
- Supports a maximum resolution of 2048x1536 with 450 Mhz bandwidth
- Switch between PC's by using the controls on the switcher or the included remote control

Technical Specifications

- Color: Black
- Connector Types: 1 - High Density DB15 Female
- Connector Types: 4 - High Density DB15 Male
- Product Height: 1.65 in [42 mm]
- Product Length: 5 in [127 mm]
- Number of Ports: 4
- Carton Quantity: 20
- Shipping (Package) Weight: 1.57 lb [0.71 kg]
- Product Weight: 17.65 oz [500 g]
- Product Width: 2.64 in [67 mm]
- Power Adapter: 5V DC, 1A
- Cable Distance (Selector to Monitor): 65 meters (max.)
- Signal Type: VGA, SVGA, XGA, Multi sync.
- Operating Temperature: 0 - 40 degrees (Celsius)
- Storage Temperature: -50 - 70 degrees (Celsius)
- Bandwidth: 450MHz