

## 4 Port Component Video Switch with RS-232

StarTech ID: VS421CPNTA



This 4 Port Component Video Switch offers convenient switching between Composite/HD video sources as well as the accompanying audio (S/PDIF (digital) or RCA (analog)).

The ideal choice for using multiple composite or component video sources with a single standard or high definition display, the video switch supports common HDTV display resolutions (480i, 576i, 480p, 576p, 720p, 1080i and 1080p). As an additional convenience, the Component video switch can be controlled using a serial connection, the front panel push-buttons, or the included IR Remote control.

### Applications and Solutions

- Any component systems like dvd players, and game consoles
- Component/composite switcher
- Ideal for home theater and presentations
- Simply pressing one button, you are able to convert between HD or SD

## Features

- controlled through input button on the front panel or using the included infrared remote control.
- High bandwidth (650 MHz at -3dB)
- IR remote control
- Plug and play
- RS232 interface allowing to control from a distance
- Supports audio formats: S/PDIF (digital) and L/R (analog)
- Supports HDTV resolution: 480i, 576i, 480p, 576p, 720p, 1080i, 1080p

## Technical Specifications

- Carton Quantity: 3
- Shipping (Package) Weight: 12.99 lb [5.88 kg]
- Input Connectors: YUV (YPbPr) x4 via 3 RCA connectors (Vpp@ 75 OHM) Composite Video x4 via coaxial connectors (0.5-1 Vpp@ 75 ohm) Stereo L/R ( Analog format) x4 via 2 RCA connectors
- Output Connectors: YUV (YPbPr) x1 via 3 RCA connectors (Vpp@ 75 OHM) Composite Video x1 via coaxial connectors (0.5-1 Vpp@ 75 ohm) Stereo L/R ( Digital format) x via 2 RCA connectors
- Bandwidth: 650 MHz (-3dB)