

Added Functionality, Increased Productivity

Wide Selection

Quickly find the right card for any application to optimize system performance.

Functionality

StarTech.com I/O cards can help you add new capabilities to your systems, helping to maximize productivity.



USB

# of Ports	Bus	Type	Data Rate	Features	Part Number	
2 Ports	Cardbus	USB 2.0	480Mbps	Laptops	CBUSB220	Ⓡ
3 Ports	Cardbus	USB 2.0	480Mbps	Laptops	CB330USB2	Ⓡ
4 Ports	Cardbus	USB 2.0	480Mbps	Laptops	CB420USB	Ⓡ
2 Ports	Express Card	USB 2.0	480Mbps	Laptops	EC230USB	Ⓡ
4 Port	Express Card	USB	480 Mbps	Laptops	EC400USB	Ⓡ
3 Ports	PCI	USB 2.0	480Mbps	2 Ext / 1 Int	PCI220USB	Ⓡ
3 Ports	PCI Low Profile	USB 2.0	480Mbps	2 Ext / 1 Int	PCI220USBLP	Ⓡ
4 Ports	PCI	USB 2.0	480Mbps	3 Ext / 1 Int	PCI330USB2	Ⓡ
5 Ports	PCI	USB 2.0	480Mbps	4 Ext / 1 Int	PCI420USB	Ⓡ
6 Ports	PCI	USB 2.0	480Mbps	4 Ext / 2 Int	PCI625USB2I	Ⓡ
5 Ports	PCI Express	USB 2.0	480Mbps	4 Ext / 1 Int	PEX400USB2	Ⓡ



5 Port PCI Express USB 2.0 Adapter Card
PEX400USB2



2 Port 1b 1a ExpressCard 34mm Laptop 1394 FireWire Adapter Card
EC13941A1B



2 Port 1b 1a ExpressCard 34mm Laptop 1394 FireWire Adapter Card
PEX1394B3

FireWire

# of Ports	Bus	Type	Data Rate	Features	Part Number	
2 Ports	Cardbus	FireWire	400Mbps	Laptops; Digital Video Kit Included	CB1394_2	Ⓡ
3 Ports	Cardbus	FireWire	400Mbps	Laptops; Digital Video Kit Included	CB1394	Ⓡ
3 Ports	Cardbus	FireWire 800	800Mbps	Laptops	CB1394B3	Ⓡ
2 Ports	Express Card	FireWire	400Mbps	Laptops	EC13942	Ⓡ
2 Ports	Express Card	FireWire	400 / 800Mbps	Laptops; 1 x 1394a / 1 x 1394b	EC13941A1B	Ⓡ
2 Ports	Express Card	FireWire 800	800Mbps	Laptops	EC1394B2	Ⓡ
3 Ports	PCI	FireWire	400Mbps	2 Ext / 1 Int; DV Kit	PCI1394_2	Ⓡ
3 Ports	PCI Low Profile	FireWire	400Mbps	2 Ext / 1 Int; DV Kit	PCI1394_2LP	Ⓡ
3 Ports	PCI	FireWire 800/400	800 / 400Mbps	2x1394b / 1x1394a; DV Kit	PCI1394B_3	Ⓡ
4 Ports	PCI	FireWire	400Mbps	3 Ext / 1 Int; DV Kit	PCI1394_4	Ⓡ
4 Ports	PCI	FireWire	400Mbps	DV Kit; PC/Mac; Incl LP Bracket	PCI1394MP	Ⓡ
2 Ports	PCI Express	FireWire	400Mbps	Single Chip; LP Bkt	PEX1394A2	Ⓡ
2 Ports	PCI Express	FireWire	400Mbps	Single Chip; DV Kit; LP Bkt	PEX1394A2DV	Ⓡ
4 Ports	PCI Express	FireWire	400Mbps	3 Ext / 1 Int; LP Bkt	PEX13943	Ⓡ
3 Ports	PCI Express	FireWire 800/400	800 / 400Mbps	2x1394b / 1x1394a; Single Chip, LP	PEX1394B3	Ⓡ

Ⓡ Retail-Ready

Combo

# of Ports	Bus	Type	Data Rate	Features	Part Number	
3 Ports	PCI	Combo	115Kbps, 1.5Mbps	2 Serial, 1 ECP/EPP Parallel	PCI2S1P	
3 Ports	ExpressCard	Combo	400Mbps; 480Mbps	Laptops; 2 Firewire; 1 USB	EC1U2F	
5 Ports	PCI	Combo	480Mbps, 400Mbps	3 USB, 2 FireWire	PCI3UV22F	Ⓡ
3 Ports	PCI Express	Combo	230.4Kbps, 1.5Mbps	2 Serial, 1 Parallel	PEX2S1P	Ⓡ
2 Ports	PCI 3.3/5.0V	Combo	920Kbps, 1.5Mbps	1 Serial, 1 Parallel	PCI2S1PDV	Ⓡ
3 Ports	PCI 3.3/5.0V	Combo	920Kbps, 1.5Mbps	2 Serial, 1 Parallel	PCI2S1PDVLP	Ⓡ

Ⓡ Retail-Ready

eSATA / SATA

# of Ports	Bus	Type	Data Rate	Features	Part Number	
2 Port	CardBus	eSATA	150 Mbps	Laptop; 2 Ext, 32 bit CardBus	CBESATA2	
2 Port	Express Card	eSATA	300 Mbps	2 Ext, Port Multiplier, Single Chip	ECESATA22	Ⓡ
2 Port	Express Card	eSATA	300 Mbps	2 Ext, Port Multiplier, Single Chip	ECESATA254	Ⓡ
2 Port	PCI	eSATA/SATA	150 Mbps	1 Internal AND 1 External	PCIESATA2I	Ⓡ
4 Port	PCI	SATA	150 Mbps	RAID 0,1; LP Bracket	PCISATA4R1	Ⓡ
2 Port	PCI Express	eSATA/SATA	300 Mbps	1 Int OR 1 Ext, PM, Single Chip; LP Bkt	PEXESATA1	Ⓡ
2 Port	PCI Express	eSATA/SATA	300 Mbps	1 Int AND 1 Ext, PM, Single Chip; LP Bkt	PEXESATA2I	Ⓡ
2 Port	PCI Express	eSATA	300 Mbps	2 Ext, PM, Single Chip; LP Bkt	PEXESATA2	Ⓡ
2 Port	PCI Express	SATA	300 Mbps	2 Port SATA, PM, Single Chip	PEXSATA22I	Ⓡ
6 Port	PCI Express	SATA/eSATA	300 Mbps	4 Int / 2 Ext, Port Multiplier	PEXSATA24E	Ⓡ

Ⓡ Retail-Ready



4 Port PCI Express x4 SATA II Card
PEXSATA24E

Ⓡ Retail-Ready

Last updated April 7th, 2009

For complete product information
Visit www.startech.com/iocards

For Customer Service Call
1-800-265-1844



IDE / SATA



1 Port PCI Express IDE Controller Adapter Card
PEX2IDE

# of Ports	Bus	Type	Data Rate	Features	Part Number
2 IDE	PCI	ATA/IDE	133 Mbps	Dual Channel - Support 4 Drives	PCIIDE2
2 IDE	PCI	Ultra ATA/100 IDE	100 Mbps	Dual Channel, RAID 0, 1, 0+1	PCIIDE100R
1 IDE	PCI Express LP	IDE/133	133 Mbps	1 Channel (2 Drives); Dual Profile	PEX2IDE
2 SATA, 1 IDE	PCI	SATA/IDE	150 Mbps	Combo, Dual Profile; LP Bracket	PCISAT2IDE1
2 SATA, 2 IDE	PCI Express	SATA/IDE	300 Mbps	Combo, Dual Channel IDE, RAID 0, 1	PEXSAT2IDE2

Bridging Adapters / Converters



ExpressCard to CardBus Laptop Adapter PC Card
CB2EC

Host to Peripheral	Host System	Bus/Connector	Features	Part Number
EC to PCMCIA/CardBus	Laptop	ExpressCard	Laptops; Wireless, Industrial, Legacy	CB2EC
PCMCIA/CardBus to EC	Laptop	CardBus	Laptops; USB-Based ExpressCard/34	EC2CBU
PCI to PCMCIA/CardBus	Desktop	PCI 3.3/5.0 V	Single Card Port; PCI or PCI-X	PCI2PCMCIA1E
PCI to PCMCIA/CardBus	Desktop	PCI 3.3/5.0 V	Dual Card Ports; PCI or PCI-X; LP Bkt	PCI2PCMCIA2
PCI to Mini PCI	Desktop	PCI 3.3/5.0 V	Mini PCI Wireless; PCI or PCI-X	PCI2MPCIB
PCI Express to ExpressCard	Desktop	PCI Express	Supports 34 and 54mm EC	PEX2EC
PCI Express to ExpressCard	Desktop	PCI Express	34 and 54mm; Std & Low Profile Bkt	PEX2ECDP
PCI Express to ExpressCard	Desktop	PCI Express	34 and 54mm; 3.5" or 5.25" Bay	PEX2EC35
PCI Express to PCI	Desktop	PCI-Express	4 Slot PCI Expansion Bay	PEX2PCI4
ExpressCard to PCI	Laptop	ExpressCard	Connect PEX2PCI4 to Laptop	EC2PCI
SATA to IDE	Desktop/Server	IDE HD to Adapter; SATA to Mb	Connect IDE HD to SATA System	SATA2ATA133
IDE to SATA	Desktop/Server	Keyed IDE Connection to Mb	Connect 2 SATA HD to IDE System	PATA2SATA2
IDE to SATA	Desktop/Server	Adapter to HD; IDE 40pin Cable from Mb	Connect SATA HD to IDE System	IDE2SAT
IDE to SATA	Desktop/Server	Adapter to IDE Mb; SATA to HD	Connect 2.5 or 3.5" SATA to IDE	IDE2SAT25
SATA to Optical IDE	Desktop/Server	Optical IDE to SATA	For Slim IDE Optical Drive	OPT2SATA



Dual Profile PCI Express to ExpressCard Adapter
PEX2ECDP

Compact Flash Adapters



Dual Profile PCI Express to ExpressCard Adapter
IDE2SAT25

Host to Peripheral	Host System	Connector	Features	Part Number
IDE to CF	Desktop	IDE 40 or 44 pin	Fits in 3.5" Bay; CF & Micro-Drive	35BAYCF2IDE
SATA to CF	Desktop	SATA Data; SP4	Fits in 3.5" Bay; CF & Micro-Drive	35BAYCF2SAT
1.8" IDE to CF	Laptop; iPod	ZIF/LIF 40 pin	Bootable Solid State Drive; CF or M-D	ZIF2CF
1.8 or 2.5" IDE to CF	Laptop	IDE 44 pin	Bootable Solid State Drive; CF or M-D	CF2IDE18
IDE 2.5" to CF	Laptop/Desktop	IDE 44 pin	Bootable SSD; Dual CF or Micro-Drives	CF2X2IDE25
SATA to CF	Laptop/Desktop	SATA 22pin (Data/Power)	Bootable Solid State Drive; CF or M-D	SAT2CF
IDE to CF	Desktop	IDE 40 or 44 pin	Bootable SSD; CF or M-D; Rear PCI	PLATEIDE2CF
IDE 3.5" to CF	Desktop	IDE 40 pin	Bootable Solid State Drive; CF or M-D	IDE2CFINT



SATA to Compact Flash SSD Adapter
SAT2CF

Media Card Readers

Type	Host System	Bus	Features	Part Number
Single Slot; 12-in-1	Laptop	ExpressCard 34/54	SD/MMC/MS/MS PRO/XD	ECREAD
Single Slot	Laptop	ExpressCard 34mm	Compact Flash & Micro-Drives	CF2EC

Video Cards



ExpressCard 12-in-1 Multi Media Memory Card
ECREAD

# of Ports	Bus	Resolution	Features	Part Number
Single VGA	PCI	1280 x 1024 (32Bit)	Server, Thin Client, Industrial	PCIVGA7

Sound Cards



4 Channel Low Profile PCI Sound Adapter Card
AC97 3D Audio Effects
PCISOUND4LP

Ports	Bus	Type	Features	Part Number
Audio Out, Line in, Mic, MIDI	PCI	4 Channel	Legacy Audio SBPro	PCISOUND4CH
Audio Out, Line in, Mic	PCI Low Profile	4 Channel	AC97 3D Audio, Incl LP Bracket	PCISOUND4LP
Audio Out, Line in, Mic, MIDI	PCI	5.1 Channel	Legacy Audio SBPro; 3D Audio; Game Port	PCISOUND5CH

SCSI Cards

# of Ports	Bus	Type	Data Rate	Features	Part Number
1 Port	PCI	Ultra Wide 68 pin	40 Mbyte/sec.	Up to 15 Wide SCSI devices supported	PCISCSIUW

Other Cards & IO



PCI Express x1 Left Slot Riser Adapter Card for Low Profile System
PCIE1RIS

Description	Part Number
PCI Express 1x Riser Card	PCIE1RIS
PCI Express 1x to 4x, 8x, 16x Low Profile Adapter	PEX1TO16
Black 3.5" Drive Bay Multi-Port Panel w/ eSATA	35BAYPANELBK
PCI Post Diagnostics Test Card	PCIPOST

