



Cables

The StarTech.com Advantage:

Huge Selection: Multiple lengths and colors available, supporting leading-edge and legacy technologies
Best Value: Your best combination of performance and price

Quality Assurance: All cables are 100% tested and backed by a lifetime warranty



Molded CAT5E Patch Cable

	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male
Length	Blue	Gray	Black	White	Red	Orange	Yellow	Purple	Green
1 ft	M45PATCH1BL	M45PATCH1GR	M45PATCH1BK	M45PATCH1WH	M45PATCH1RD		M45PATCH1YL		
2 ft	M45PATCH2BL	M45PATCH2GR	M45PATCH2BK	M45PATCH2WH	M45PATCH2RD		M45PATCH2YL		M45PATCH2GN
3 ft	M45PATCH3BL	M45PATCH3GR	M45PATCH3BK	M45PATCH3WH	M45PATCH3RD	M45PATCH3OR	M45PATCH3YL	M45PATCH3PL	M45PATCH3GN
5 ft	M45PATCH5BL	M45PATCH5GR							
6 ft	M45PATCH6BL	M45PATCH6GR	M45PATCH6BK	M45PATCH6WH	M45PATCH6RD	M45PATCH6OR	M45PATCH6YL	M45PATCH6PL	M45PATCH6GN
7 ft	M45PATCH7BL	M45PATCH7GR							
10 ft	M45PATCH10BL	M45PATCH10GR	M45PATCH10BK	M45PATCH10WH	M45PATCH10RD	M45PATCH10OR	M45PATCH10YL	M45PATCH10PL	M45PATCH10GN
15 ft	M45PATCH15BL	M45PATCH15GR	M45PATCH15BK	M45PATCH15WH	M45PATCH15RD	M45PATCH15OR	M45PATCH15YL	M45PATCH15PL	M45PATCH15GN
20 ft	M45PATCH20BL	M45PATCH20GR							
25 ft	M45PATCH25BL	M45PATCH25GR	M45PATCH25BK	M45PATCH25WH	M45PATCH25RD	M45PATCH25OR	M45PATCH25YL	M45PATCH25PL	M45PATCH25GN
35 ft	M45PATCH35BL	M45PATCH35GR	M45PATCH35BK	M45PATCH35WH					
50 ft	M45PATCH50BL	M45PATCH50GR	M45PATCH50BK	M45PATCH50WH	M45PATCH50RD	M45PATCH50OR	M45PATCH50YL	M45PATCH50PL	M45PATCH50GN
75 ft	M45PATCH75BL	M45PATCH75GR	M45PATCH75BK	M45PATCH75WH					
100 ft	M45PATCH100B	M45PATCH100G	M45PATCH100K	M45PATCH100W	M45PATCH100R		M45PATCH100Y		M45PATCH100GN
Other Network Patch Cables									
CAT5E Shielded Patch Cable	S45PATCHXXBL								
CAT5E Crossover Snagless Patch Cable	RJ454CROSSXX								
CAT5E Snagless Patch Cable	RJ45PATCHXX		45PATCHXXBK	45PATCHXXWH	45PATCHXXRD	45PATCHXXOR	45PATCHXXYL		
CAT5E Molded Crossover Patch Cable	M45CROSSXXBL								
CAT5E Flat Molded Patch Cable	FLAT45BLXX	FLAT45GRXX	FLAT45BKXX						
CAT6 Molded Patch Cable	C6PATCHXXBL	C6PATCHXXGR	C6PATCHXXBK	C6PATCHXXWH			C6PATCHXXYL	C6PATCHXXPL	
CAT6 Crossover Molded Patch Cable							C6CROSSXXYL		

XX=length

Molded Snagless CAT5E Patch Cable

	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male	RJ45 - Male
Length	Blue	Gray	Black	White	Red	Orange	Green	Yellow
1 ft	RJ45PATCH1	45PATCH1GR						
2 ft	RJ45PATCH2	45PATCH2GR			45PATCH2RD			
3 ft	RJ45PATCH3	45PATCH3GR	45PATCH3BK	45PATCH3WH	45PATCH3RD	45PATCH3OR	45PATCH3GN	45PATCH3YL
4 ft	RJ45PATCH4							
5 ft	RJ45PATCH5	45PATCH5GR						
6 ft	RJ45PATCH6	45PATCH6GR	45PATCH6BK	45PATCH6WH	45PATCH6RD	45PATCH6OR	45PATCH6GN	45PATCH6YL
7 ft	RJ45PATCH7	45PATCH7GR						
10 ft	RJ45PATCH10	45PATCH10GR	45PATCH10BK	45PATCH10WH	45PATCH10RD	45PATCH10OR	45PATCH10GN	45PATCH10YL
12 ft	RJ45PATCH12	45PATCH12GR						
15 ft	RJ45PATCH15	45PATCH15GR	45PATCH15BK	45PATCH15WH	45PATCH15RD	45PATCH15OR	45PATCH15GN	45PATCH15YL
20 ft	RJ45PATCH20	45PATCH20GR						
25 ft	RJ45PATCH25	45PATCH25GR	45PATCH25BK	45PATCH25WH	45PATCH25RD	45PATCH25OR	45PATCH25GN	45PATCH25YL
35 ft	RJ45PATCH35	45PATCH35GR						
50 ft	RJ45PATCH50	45PATCH50GR	45PATCH50BK	45PATCH50WH	45PATCH50RD		45PATCH50GN	
75 ft	RJ45PATCH75	45PATCH75GR						
100 ft	RJ45PATCH100	45PATCH100GR	45PATCH100BK	45PATCH100WH	45PATCH100RD		45PATCH100GN	45PATCH100YL

For more information on our complete line of cables visit www.startech.com/cables

Last updated January 12, 2006



The StarTech.com Advantage:

Huge Selection: Multiple lengths and colors available, supporting leading-edge and legacy technologies
Best Value: Your best combination of performance and price

Quality Assurance: All cables are 100% tested and backed by a lifetime warranty



Fiber Optic



ST



LC



MT-RJ



SC



SC Duplex

LC-LC	LC-MT	LC-SC	MT-MT	MT-SC	MT-ST	SC-SC	ST-ST	Cable Type	Fiber Size	UL Rated	Cable Length
50FIBLCLC1	50FIBLCMT1	50FIBLCSC1	50FIBMTMT1	50FIBSCMT1		50FIBSCSC1		Multimode	50 Micron	Yes	3.3ft / 1m
50FIBLCLC2	50FIBLCMT2	50FIBLCSC2	50FIBMTMT2	50FIBSCMT2		50FIBSCSC2		Multimode	50 Micron	Yes	6.6ft / 2m
50FIBLCLC3	50FIBLCMT3	50FIBLCSC3	50FIBMTMT3	50FIBSCMT3		50FIBSCSC3		Multimode	50 Micron	Yes	9.8ft / 3m
50FIBLCLC5	50FIBLCMT5	50FIBLCSC5	50FIBMTMT5	50FIBSCMT5		50FIBSCSC5		Multimode	50 Micron	Yes	16.5ft / 5m
50FIBLCLC10	50FIBLCMT10	50FIBLCSC10	50FIBMTMT10	50FIBSCMT10		50FIBSCSC10		Multimode	50 Micron	Yes	33ft / 10m
FIBLCLC1	FIBLCMT1	FIBLCSC1	FIBMTMT1	FIBMTSC1	FIBMTST1	FIBSCSC1	FIBSTST1	Multimode	62.5 Micron	Yes	3.3ft / 1m
FIBLCLC2	FIBLCMT2	FIBLCSC2	FIBMTMT2	FIBMTSC2	FIBMTST2	FIBSCSC2	FIBSTST2	Multimode	62.5 Micron	Yes	6.6ft / 2m
FIBLCLC3	FIBLCMT3	FIBLCSC3	FIBMTMT3	FIBMTSC3	FIBMTST3	FIBSCSC3	FIBSTST3	Multimode	62.5 Micron	Yes	9.8ft / 3m
FIBLCLC5	FIBLCMT5	FIBLCSC5	FIBMTMT5	FIBMTSC5	FIBMTST5	FIBSCSC5	FIBSTST5	Multimode	62.5 Micron	Yes	16.5ft / 5m
FIBLCLC7	FIBLCMT7	FIBLCSC7	FIBMTMT7	FIBMTSC7	FIBMTST7	FIBSCSC7	FIBSTST7	Multimode	62.5 Micron	Yes	23.1ft / 7m
FIBLCLC10	FIBLCMT10	FIBLCSC10	FIBMTMT10	FIBMTSC10	FIBMTST10	FIBSCSC10	FIBSTST10	Multimode	62.5 Micron	Yes	33ft / 10m
FIBLCLC15	FIBLCMT15	FIBLCSC15	FIBMTMT15	FIBMTSC10	FIBMTST10	FIBSCSC15	FIBSTST15	Multimode	62.5 Micron	Yes	49.5ft / 15m
						FIBSCSC20	FIBSTST20	Multimode	62.5 Micron	Yes	66ft / 20m
						FIBSCSC30		Multimode	62.5 Micron	Yes	99ft / 30m
						FIBSCSC40		Multimode	62.5 Micron	Yes	132ft / 40m
						FIBSCSC50	FIBSTST50	Multimode	62.5 Micron	Yes	165ft / 50m
		SMFIBLCSC1		SMFIBSTSC1		SMFIBSCSC1	SMFIBSTST1	Singlemode	9 Micron	Yes	3.3ft / 1m
				SMFIBSTSC2		SMFIBSCSC2	SMFIBSTST2	Singlemode	9 Micron	Yes	6.6ft / 2m
				SMFIBSTSC3		SMFIBSCSC3	SMFIBSTST3	Singlemode	9 Micron	Yes	9.8ft / 3m
				SMFIBSTSC5		SMFIBSCSC5	SMFIBSTST5	Singlemode	9 Micron	Yes	16.5ft / 5m
				SMFIBSTSC10		SMFIBSCSC10	SMFIBSTST10	Singlemode	9 Micron	Yes	33ft / 10m
				SMFIBSTSC15		SMFIBSCSC15	SMFIBSTST15	Singlemode	9 Micron	Yes	49.5ft / 15m
				SMFIBSTSC20		SMFIBSCSC20	SMFIBSTST20	Singlemode	9 Micron	Yes	66ft / 20m
				SMFIBSTSC30		SMFIBSCSC30	SMFIBSTST30	Singlemode	9 Micron	Yes	99ft / 30m

USB

Length	USB 2.0 Type A Type B	USB 2.0 Type A Type B	USB 1.1 Type A Type B	USB 1.1 Type A Type B	USB 2.0 Type A Mini B	USB 2.0 Type A Mini B	USB 2.0 Extension Type A Type A	USB 1.1 Extension Type A Type A	USB 1.1 Active Extension Type A Type A
6 inches	Black	Transparent	Beige	Transparent	Gray	Black	Beige	Beige	Beige
1 ft	USB2HAB1						USBEXTAA6IN		
3 ft			USBFAB_3	USBFAB_3T	USB2HABM3	USBFA4S3			
6 ft	USB2HAB6	USB2HAB6T	USBFAB_6	USBFAB_6T	USB2HABM6	USBFA4S6	USBEXTAA_6	USBFAA_6	
10 ft	USB2HAB10	USB2HAB10T	USBFAB_10	USBFAB_10T	USB2HABM10	USBFA4S10			
15 ft	USB2HAB15	USB2HAB15T	USBFAB_15	USBFAB_15T					USBFAEXT15A

FireWire

Length	IEEE 1394 6 pin 6 pin	IEEE 1394 6 pin 6 pin	IEEE 1394 4 pin 4 pin	IEEE 1394 4 pin 6 pin	IEEE 1394 4 pin 6 pin	IEEE 1394b 9 pin 4 pin	IEEE 1394b 9 pin 6 pin	IEEE 1394b 9 pin 9 pin
6 ft	Black	Transparent	Black	Black	Transparent	Black	Black	Black
6 ft	1394_6		1394_44_6	1394_46_6	1394_46_6T	1394_94_6	1394_96_6	1394_99_6
10 ft	1394_10	1394_10T	1394_44_10	1394_46_10		1394_94_10	1394_96_10	1394_99_10
15 ft	1394_15	1394_15T	1394_44_15	1394_46_15				

Video/Monitor

Length	DVI-D Single Link Male - Male	DVI-D Single Link Extension Male - Female	DVI-D Dual Link Male - Male	DVI-D Dual Link Extension Male - Female	DVI-I Single Link Male - Male	DVI-I Dual Link Male - Male	DVI-I Dual Link Extension Male - Female	SVGA Monitor Male - Male	SVGA Monitor Extension Male - Female
6 ft	Black	Black	Black	Black	Black	Black	Black	Black	Black
6 ft	DVIIMM6	DVIDSMF6	DVIDDMM6	DVIDDMF6	DVIISMM6	DVIIDMM6	DVIIDMF6	MXT101MMHQ	MXT101HQ
10 ft	DVIDSMM10	DVIDSMF10	DVIDDMM10	DVIDDMF10	DVIISMM10	DVIIDMM10	DVIIDMF10	MXT101MMHQ10	MXT101HQ10
15 ft	DVIDSMM15	DVIDSMF15	DVIDDMM15		DVIISMM15	DVIIDMM15	DVIIDMF15	MXT105MMHQ	MXT105HQ
20 ft	DVIDSMM20		DVIDDMM20						
25 ft								MXT101MMHQ25	MXT101HQ_25
50 ft								MXT101MMHQ50	MXT101HQ_50
100 ft									MXT101HQ_100
150 ft									MXT101HQ_150
200 ft									MXT101HQ_200

For more information on our complete line of Cables visit www.startech.com/cables

Last updated January 12, 2006