

1 ft IEEE-1394 Firewire Cable 4-6 M/M

StarTech ID: 139446MM1



This 1ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV Camcorder to a computer, etc.).

Applications

- Connect a external FireWire hard drive enclosure to a Notebook or PC
- Connect a FireWire camera or video recorder to a Notebook or PC
- Perfect for portable FireWire applications

Features

- Molded connector strain relief
- Short, portable cable design
- IEEE 1394a Standards Compliant

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector A	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Connector B	1 - Firewire 400 (6 pin; IEEE 1394a) Male
Type and Rate	FireWire 400 IEEE-1394a - 400 Mbit/s
Color	Black
Wire Gauge	30 AWG
Cable Length	1 ft [0.3 m]
Shipping (Package) Weight	1.8 oz [50 g]
Included in Package	1 - 1 Ft. IEEE-1394 Firewire Cable 4-6 Pin

Certifications, Reports and Compatibility

