

15 ft Transparent IEEE-1394 Firewire Cable 6-6 M/M

StarTech ID: 1394_15T



This 15ft transparent/clear IEEE-1394 rated FireWire cable provides the high-speed link required for today's demanding peripherals.

The cable features 6-pin FireWire connectors on both ends and see-through sheathing that blends quietly into any environment.

Compatible with all 6-pin FireWire and iLink devices.

Applications and Solutions

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

Features

- 6-pin cable draws power from firewire bus
- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Hot Pluggable; allows swapping of live devices
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference
- Supports a daisy-chain of up to 63 firewire devices
- Supports Plug and Play
- Transparent color blends into any environment
- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Up to 400 Mbits/sec data transfer rate

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 6 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Transparent
- Product Length: 15 ft [4.57 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 100
- Shipping (Package) Weight: 0.66 lb [0.3 kg]
- Connector A: 6-pin Male
- Connector B: 6-pin Male
- Color: Transparent
- Length: 15ft (4.6m)
- IEE1394-1995 Compliant:

