

15 ft IEEE-1394 Firewire Cable 4-4 M/M

StarTech ID: 1394_44_15



This 15ft 1394 FireWire (400) Cable features two 1394 (4-pin) male connectors and supports full FireWire 400 data transfer rates of up to 400Mbps, to provide a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Backed by StarTech.com's Lifetime Warranty, this cable is expertly designed and constructed of only IEEE-1394 rated wire for full FireWire 400 compatibility and reliability.

Technical Specifications

Warranty	Lifetime
Connector A	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Connector B	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Black
Product Length	15 ft [4.6 m]
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - 15 Ft. IEEE-1394 Firewire Cable 4-4 M/M

Certifications, Reports and Compatibility

