

6ft IEEE-1394 FireWire Cable 4 - 4 M/M

StarTech ID: 1394_44_6



This 6ft IEEE 1394 FireWire Cable provides two 4-pin FireWire male connectors and is expertly designed and constructed of high quality materials to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Backed by StarTech.com's Lifetime Warranty, this high quality cable is manufactured using IEEE-1394 rated wire for full FireWire 400 reliability and compatibility.

Technical Specifications

Warranty	Lifetime
Connector A	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Connector B	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Black
Product Length	6 ft [1.8 m]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - 6 Ft. IEEE-1394 Firewire Cable 4-4 M/M

Certifications, Reports and Compatibility

