

15 ft IEEE-1394 Firewire Cable 4-6 M/M

StarTech ID: 1394_46_15



This 15ft IEEE 1394 FireWire Cable provides one FireWire 4-pin male connector and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, 1394a FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Backed by StarTech.com's Lifetime Warranty, this high quality FireWire Cable is manufactured using IEEE-1394 rated wire for full FireWire 400 reliability and compatibility.

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Black
- Product Length: 15 ft [4.57 m]

- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 100
- Shipping (Package) Weight: 0.42 lb [0.19 kg]

