

6 ft IEEE-1394 Firewire Cable 4-6 M/M

StarTech ID: 1394_46_6



This 6ft IEEE 1394 FireWire Cable provides one FireWire 4-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Black
- Product Length: 6 ft [1.83 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 150
- Shipping (Package) Weight: 0.22 lb [0.1 kg]

- Connectors: IEEE-1394 4-pin Male, IEEE-1394 6-pin Male
- Length: 6 ft. [1.83 m]

