

6 ft Transparent IEEE-1394 Firewire Cable 4-6 M/M

StarTech ID: 1394_46_6T



This 6ft clear 1394 FireWire cable features a 4-to-6 pin (M-M) configuration that delivers a reliable link for today's demanding FireWire peripheral connections.

The FireWire 400 cable also offers an attractive clear (transparent) sheathing that blends discreetly into any operating environment.

Applications and Solutions

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

Features

- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Hot Pluggable; allows swapping of live devices
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference
- Supports a daisy-chain of up to 63 firewire devices
- Supports Plug and Play
- Transparent color blends into any environment
- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Up to 400 Mbits/sec data transfer rate

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 4 pin Male
- Connector B: 1 - Firewire 6 pin Male
- Color: Transparent
- Product Length: 6 ft [1.83 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 150
- Shipping (Package) Weight: 0.22 lb [0.1 kg]
- Connector A: 4-pin Male
- Connector B: 6-pin Male
- Color: Transparent
- Length: 6ft (1.8m)
- IEE1394-1995 Compliant:

