

6 ft Transparent IEEE-1394 Firewire Cable 4-6 M/M

StarTech ID: 1394_46_6T



This 6ft clear 1394 FireWire cable features a 4-to-6 pin (M-M) configuration that delivers a reliable link for today's demanding FireWire peripheral connections.

The FireWire 400 cable also offers an attractive clear (transparent) sheathing that blends discreetly into any operating environment.

Applications

- Connect a Digital camcorder or other IEEE-1394 device to a computer at high-performance data transfer speed
- Connect multiple firewire compliant devices together

Features

- Transparent color blends into any environment
- Up to 400 Mbits/sec data transfer rate
- Supports Plug and Play
- Hot Pluggable; allows swapping of live devices
- Compatible with all PC Firewire, Apple Firewire, and Sony iLink devices
- Supports a daisy-chain of up to 63 firewire devices
- Twisted-pair and quad shielding (S-400 specification) cable components ensure error-free and high-speed data transfer with no data loss
- Outer shield and inner shield (foil and braid) complies with latest IEEE-1394 standards, resulting in minimal radio and electro-magnetic interference

Technical Specifications

Warranty	Lifetime
Industry Standards	IEE1394-1995 Compliant
Connector A	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Connector B	1 - Firewire 400 (6 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Transparent
Product Length	6 ft [1.8 m]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - 6 ft. Transparent Firewire Cable 4-6 Pin

Certifications, Reports and Compatibility

