

6ft IEEE-1394 FireWire Cable 6-6 M/M

StarTech ID: 1394_6



This 6ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a dv camcorder to a computer, etc.).

Technical Specifications

Warranty	Lifetime
Connector A	1 - Firewire 400 (6 pin; IEEE 1394a) Male
Connector B	1 - Firewire 400 (6 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Gray
Product Length	6 ft [1.8 m]
Shipping (Package) Weight	0.3 lb [0.1 kg]
Included in Package	1 - FIREWIRE CABLE

Certifications, Reports and Compatibility

