

## 6 ft IEEE-1394 Firewire Cable 9-4 M/M

StarTech ID: 1394\_94\_6



This 6ft 1394b FireWire cable provides one FireWire 800 9-pin male connector and one FireWire 4-pin male connector, allowing you to connect your FireWire 400 devices to your FireWire 800 ports - ensuring that your high speed digital storage and video capture applications will be running at their peak.

Expertly designed to provide a high quality, long-lasting FireWire connection, the 1394b FireWire (4 pin to 9 pin) cable is backed by StarTech.com's Lifetime Warranty.

### Applications

- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products
- Connect multiple FireWire devices together

### Features

- Fast data transfer rate of up to 800 Mbts/sec
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Compliant with 1394a & 1394b standards
- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Supports a daisy-chain of up to 63 fireWire devices
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Twisted Pair Construction

## Technical Specifications

Warranty	Lifetime
Industry Standards	IEEE 1394a & 1394b
Connector A	1 - Firewire 800 (9 pin; IEEE 1394b) Male
Connector B	1 - Firewire 400 (4 pin; IEEE 1394a) Male
Maximum Cable Length	14 ft [4.3 m]
Color	Black
Product Length	6 ft [1.8 m]
Shipping (Package) Weight	0.2 lb [0.1 kg]
Included in Package	1 - 6 ft IEEE-1394 Firewire Cable 9-4 M/M

## Certifications, Reports and Compatibility

