

10 ft IEEE-1394 Firewire 800 Cable 9-6 M/M

StarTech ID: 1394_96_10



This 10ft IEEE 1394b FireWire 800 Cable provides one FireWire 9-pin and one FireWire 6-pin male connector and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 800Mbps, FireWire 800 (IEEE 1394b) technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

This high quality FireWire cable is compatible with all 1394a & 1394b PC FireWire (400/800), Apple FireWire, and Sony iLink devices and is backed by StarTech.com's Lifetime Warranty.

Applications and Solutions

- Connect multiple FireWire devices together
- Ideal for Mass storage, Digital Video (DV), Digital Audio, Digital Cameras, Printers, Scanners, Home entertainment and other Networking products

Features

- Compatible with all 1394a & 1394b PC FireWire, Apple FireWire, and Sony iLink devices
- Compliant with 1394a & 1394b standards
- Fast data transfer rate of up to 800 Mbits/sec
- Highest quality shielding protects from EMI (electromagnetic interference) noise
- Hot Pluggable feature allows swapping of live devices without turning off your computer
- Supports a daisy-chain of up to 63 fireWire devices
- Twisted Pair Construction

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - Firewire 800 9 pin Male
- Connector B: 1 - Firewire 800 9 pin Male
- Color: Black
- Product Length: 10 ft [3.05 m]
- Maximum Cable Length: 14 ft [4.27 m]
- Carton Quantity: 120
- Shipping (Package) Weight: 0.38 lb [0.17 kg]
- Cable Length: 10 Feet (3 Meters)
- Connector A: : 1394b 9 pin Male
- Connector B: 1394a 6 pin Male
- Compliant Standard: IEEE 1394a & 1394b
- Color: Black

